

Eaton Z48N11B15CU

Catalog Number: Z48N11B15CU

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPZ, copper, NEMA 3R, 180H, 60 Hz, single-phase, 480 V, 120/240 V, NONE, 80 °C rise, 15 KVA, indoor-outdoor, 524H



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48N11B15CU
	UPC
	786680056741

Product Length/Depth	Product Height
10.53 in	19.68 in

Product Width	Product Weight
19.63 in	300 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Copper

Frequency rating

50/60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

80 °C rise

Design

EPZ

Enclosure

NEMA 3R

Frame

180H

Tap size

None

Volt ampere rating

15 kVA

Weathershield

Indoor-Outdoor

Wiring connection

524H

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48N11B15CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)