

Eaton Z48N11S03A

Catalog Number: Z48N11S03A

Class 1 Division 2 Groups A, B, C and D, Hazardous Location Transformer, EPZ, Single-phase, PV: 480V, Taps: None, SV: 120/240V, 115°C, 3 kVA, Al windings, Frame: 176H, Indoor-Outdoor



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48N11S03A
	UPC
	786680006173

Product Length/Depth	Product Height
8 in	11.06 in

Product Width	Product Weight
7.69 in	74 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Class I, Div. 2, Groups A, B, C, D from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed

Catalog Notes
Model A

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Aluminum

Frequency rating

50/60 Hz

Kva Rating

3 kVA

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Design

EPZ

Enclosure

NEMA 3R

Frame

176H

Tap size

None

Volt ampere rating

3 kVA

Weathershield

Indoor-Outdoor

Wiring connection

524H

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48N11S03A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)