

Eaton Z48N11S03SS

Catalog Number: Z48N11S03SS

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPZ, aluminum, NEMA 3R, 176H, 60 Hz, single-phase, 480 V, 120/240 V, NONE, 115 °C rise, 3 KVA, indoor-outdoor, 524H



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48N11S03SS
	UPC
	786680006357
Product Length/Depth	Product Height
8.03 in	14.47 in
Product Width	Product Weight
12.5 in	80 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Grade 304 stainless steel enclosure

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Aluminum

Frequency rating

50/60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Design

EPZ

Enclosure

NEMA 3R

Frame

176H

Tap size

None

Volt ampere rating

3 kVA

Weathershield

Indoor-Outdoor

Wiring connection

524H

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48N11S03SS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)