

Eaton Z48N11S07A

Catalog Number: Z48N11S07A

Eaton Class 1 Division 2 Groups C and D, Hazardous Location Transformer, EPZ, Single-phase, PV: 480V, Taps: None, SV: 120/240V, 115°C, 7.5 kVA, Al windings, Frame: 178H, Indoor-Outdoor.



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48N11S07A
	UPC
	786680006197
Product Length/Depth	Product Height
9.89 in	16.53 in
Product Width	Product Weight
15.54 in	146 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Model A

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Aluminum

Frequency rating

50/60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Design

EPZ

Enclosure

NEMA 3R

Frame

178H

Tap size

None

Volt ampere rating

7.5 kVA

Weathershield

Indoor-Outdoor

Wiring connection

524H

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48N11S07A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)