

Eaton Z48N11S25A

Catalog Number: Z48N11S25A

Class 1 Division 2 Groups A, B, C, D Hazardous Location Transformer, Single-phase, PV: 480V, Taps: None, SV: 120/240V, 115°C, 25 kVA, Al windings, Frame: 182H, Indoor-Outdoor

Photo is representative



General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z48N11S25A
	UPC
	786680006227
Product Length/Depth	Product Height
14.1 in	23.47 in
Product Width	Product Weight
22.6 in	409 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year Not Applicable from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	Model A

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location Transformer

Coil material

Aluminum

Frequency rating

50/60 Hz

Phase

Single-phase

Primary voltage

480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Design

EPZ

Enclosure

NEMA 3R

Frame

182H

Tap size

None

Volt ampere rating

25 kVA

Weathershield

Indoor-Outdoor

Wiring connection

524H

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z48N11S25A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)