

# Eaton Z48N11S51A

Catalog Number: Z48N11S51A

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPZ, aluminum, NEMA 3R, 57H, 60 Hz, single-phase, 480 V, 120/240 V, NONE, 115 °C rise, 0.5 KVA, indoor-outdoor, 524H



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Hazardous location encapsulated transformer	Z48N11S51A
	<b>UPC</b>
	786680006128

<b>Product Length/Depth</b>	<b>Product Height</b>
4.88 in	10.11 in

<b>Product Width</b>	<b>Product Weight</b>
9.72 in	21 lb

<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

[Catalog Notes](#)  
Model A

## defaultTaxonomyAttributeLabel

### Type

Class 1 Division 2 Groups C and D, Hazardous Location  
Transformer

### Coil material

Aluminum

### Frequency rating

50/60 Hz

### Phase

Single-phase

### Primary voltage

480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Design

EPZ

### Enclosure

NEMA 3R

### Frame

57H

### Tap size

None

### Volt ampere rating

0.5 kVA

### Weathershield

Indoor-Outdoor

### Wiring connection

524H

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - Z48N11S51A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)