

Eaton Z52G28T45CU

Catalog Number: Z52G28T45CU

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups a b c and d hazardous location transformer, EPTZ, copper, 244H, 60 Hz, three-phase, 460 V, 208Y/120 V, 2 at -5% FCBN, 115 °C rise, 45 KVA, indoor-outdoor, 66l



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z52G28T45CU
	UPC
	786680115752

Product Length/Depth	Product Height
0.001 in	0.001 in

Product Width	Product Weight
0.001 in	908 lb

Warranty	Certifications
----------	----------------

Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups A B C & D Hazardous Location
Transformer

Coil material

Copper

Frequency rating

50/60 Hz

Phase

Three-phase

Primary voltage

460 V

Secondary Voltage

208Y/120 V

Temperature rise

115 °C rise

Design

EPTZ

Frame

244H

Tap size

2 at -5% FCBN

Volt ampere rating

45 kVA

Weathershield

Indoor-Outdoor

Wiring connection

66I

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z52G28T45CU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)