

Eaton Z57N11S10

Catalog Number: Z57N11S10

Eaton Hazardous location encapsulated transformer, class 1 division 2 groups c and d, hazardous location transformer, EPZ, aluminum, NEMA 3R, 179H, 60 Hz, single-phase, 575 V, 120/240 V, NONE, 115 °C rise, 10 KVA, indoor-outdoor, 524L

Photo is representative



General specifications

Product Name	Catalog Number
Eaton Hazardous location encapsulated transformer	Z57N11S10
	UPC
	786680056451
Product Length/Depth	Product Height
10.53 in	19.68 in
Product Width	Product Weight
19.63 in	244 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Type

Class 1 Division 2 Groups C and D, Hazardous Location
Transformer

Coil material

Aluminum

Frequency rating

50/60 Hz

Phase

Single-phase

Primary voltage

575 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Design

EPZ

Enclosure

NEMA 3R

Frame

179H

Tap size

None

Volt ampere rating

10 kVA

Weathershield

Indoor-Outdoor

Wiring connection

524L

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - Z57N11S10](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)