



Cat. No. 630, 630L



Cat. No. 632L

Low Voltage Push Buttons

Plastic Rust Proof Case, Illuminated & Non-Illuminated

630, 630L, 631 & 632L

FEATURES

- > Surface mounted
- > Piano type action
- > Plastic case - rust proof

Patented piano-action design requires only the slightest touch. This modern, slim design can be easily installed in minutes.

For home, apartment, office, and OEMs. Use wherever low voltage, economical remote control is required.

SPECIFICATIONS

- > 630 & 631 non-illuminated push buttons voltage: up to 48V AC
- > 630L illuminated push button voltage: up to 16V AC
- > 632L illuminated push button voltage: up to 16V AC
- > Normally open momentary contacts

Cat. No.	Style	Finish		Dimensions		
		Housing	Center	W	H	D
630	Non-illuminated	Brown	Ivory	7/8"	2 7/8"	5/8"
630L	Illuminated	Brown	Ivory	(22mm)	(73mm)	(16mm)
631	Non-illuminated	Ivory	Ivory			
632L	Illuminated	Chrome	Ivory	7/8"	2 7/8"	5/8"
				(22mm)	(73mm)	(16mm)

D-04