

Fluorescent Lamps

Linear Fluorescent Lamps

T8 U-Bend Fluorescent Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Special Desc	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
F31T8/830/U	05287	G13	22.5/571	8	U-Bend 1-5/8 inch centers, Universal Start	31	3000	20000	84	2750	2475
F31T8/835/U	05288	G13	22.5/571	8	U-Bend 1-5/8 inch centers, Universal Start	31	3500	20000	84	2750	2475
F31T8/841/U	05289	G13	22.5/571	8	U-Bend 1-5/8 inch centers, Universal Start	31	4100	20000	84	2750	2475
F31T8/850/U	05290	G13	22.5/571	8	U-Bend 1-5/8 inch centers, Universal Start	31	5000	20000	84	2625	2365
F32T8/835K/U6	02403	G13	22.5/571	9	U-Bend 6 inch centers, Universal Start	32	3500	20000	85	2800	2535
F32T8/841K/U6	02404	G13	22.5/571	9	U-Bend 6 inch centers, Universal Start	32	4100	20000	85	2800	2535
F32T8/850K/U6	02405	G13	22.5/571	9	U-Bend 6 inch centers, Universal Start	32	5000	20000	85	2750	2500

Circular Fluorescent Lamps



Ordering Code	Bar Code	Base	MOL	mg Hg	Watts	CT deg K	Life Hours	CRI	Approx Initial Lumens	Approx Mean Lumens
FC8T9/CW	15604	G10q	8.25/215	8	22	4100	12000	60	1100	825
FC8T9/D	15532	G10q	8.25/215	8	22	6500	12000	75	925	690
FC12T9/CW	15606	G10q	12.0/305	8	32	4100	12000	60	1950	1460
FC12T9/D	15533	G10q	12.0/305	8	32	6500	12000	75	1675	1260
FC16T9/CW	15534	G10q	16.0/406	8	40	4100	12000	60	2700	2030
FC16T9/D	15535	G10q	16.0/406	8	40	6500	12000	75	2250	1690

Fluorescent Starters



Ordering Code	Bar Code	Description
FS-2	49550	14 15 20W 120V Aluminum Case UL
FS-4	49551	30 40W 120V Aluminum Case
FS-5	49552	4 6 8W 120V Aluminum Case UL
FS-U-120V	49554	4 - 30W 120V Aluminum Case UL

Halogen Lamps

A-Line Halogen Lamps

EiKON Energy Efficient Halogen Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
29A/CL/H-120V	07757	29	120	A-19	Medium Screw (E26)	CC-8	430	4.25/108	2.36/60	1000
43A/CL/H-120V	07758	43	120	A-19	Medium Screw (E26)	CC-8	750	4.25/108	2.36/60	1000
53A/CL/H-120V	07759	53	120	A-19	Medium Screw (E26)	CC-8	1050	4.25/108	2.36/60	1000
72A/CL/H-120V	07760	72	120	A-19	Medium Screw (E26)	CC-8	1490	4.25/108	2.36/60	1000

Classic BT15 Halogen Lamps

Ordering Code	Bar Code	Watts	Volts	Shape	Base	Filament	Lumens	MOL	MOD	Life Hours
60BT15/H/CL	81138	60	120	BT-15	Medium Screw (E26)	CC-8	900	4.0/101	1.9/48.3	3000
60BT15/H/W	81137	60	120	BT-15	Medium Screw (E26)	CC-8	840	4.0/101	1.9/48.3	3000
75BT15/H/W	81139	75	120	BT-15	Medium Screw (E26)	CC-8	1120	4.0/101	1.9/48.3	3000
150BT15/H/W	81141	150	120	BT-15	Medium Screw (E26)	CC-8	2850	4.0/101	1.9/48.3	1500

MR8 Halogen Lamps



Ordering Code	Bar Code	Watts	Volts	Base	Filament	MOL	MOD	Life Hours	Beam Angle
Q10MR8/NSP/CG	06240	10	6	GU4	C-8	1.56/39.5	0.99/25.2	2000	10
Q20MR8/NFL/CG	05042	20	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	20
Q20MR8/NSP/CG	04977	20	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	10
Q35MR8/NFL/CG	06242	35	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	20
Q35MR8/NSP/CG	06241	35	12	GU4	C-8	1.56/39.5	0.99/25.2	2000	10