



5000 Series

FEATURES:

- Ideal for indoor and outdoor use
- Weatherproof NEMA 4X slip ring enclosure
- Heavy all-steel construction
- Numbered terminal blocks for simplified hookup
- Formed steel stand with multiple mounting holes
- Guide arm (4-roller, adjustable to 12 positions for efficient cable storage)
- Ratchet - positive lock including constant tension feature
- 35 Amp/600 volt slip ring
- Available in welding & grounding reel version
- Supplied with Type SOOW cable installed
- Primary feeder cord with watertight cable gland supplied with reel
- Ratchet & ball stop included

5000 Series Cord Reels Selection Guide

SOW Cable Gauge & Conductors - 600V

	Amp Rating	20'	30'	40'	50'	60'
16/3	10A	5163-20	5163-30	5163-40	5163-50	5163-60
16/4	8A	5164-20	5164-30	5164-40	5164-50	5164-60
16/6	8A	5166-20	5166-30	5166-40	5166-50	
16/8	7A	5168-20	5168-30	5168-40	5168-50	
16/10	5A	51610-20	51610-30	51610-40		
16/12	5A	51612-20	51612-30	51612-40		
14/3	15A	5143-20	5143-30	5143-40	5143-50	5143-60
14/4	12A	5144-20	5144-30	5144-40	5144-50	5144-60
14/6	12A	5146-20	5146-30	5146-40	5146-50	
14/8	10.5A	5148-20	5148-30			
14/10	7.5A	51410-20				
12/3	20A	5123-20	5123-30	5123-40	5123-50	5123-60
12/4	16A	5124-20	5124-30	5124-40	5124-50	
12/6	16A	5126-20	5126-30			
12/8	14A	5128-20				
10/3	25A	5103-20	5103-30	5103-40	5103-50	
10/4	20A	5104-20	5104-30	5104-40	5104-50	
10/6	20A	5106-20	5106-30			

For Reel Dimensions, refer to the end of this section.

Add-Ons - Add to Base Part Number (Call for Details)

-BG-20

Not for #16 AWG



-1612-PWDX

20 Amp
5-20R
Slot 1612-PWDX
(Not for #16 AWG)



-HSS

Handlamp for
any 3-wire cord
(Not for #16 AWG)



-F

13 watt
Fluorescent
Handlamp