

STP4A-4141A024M (ORDER NO. 099314)


Safety switch STP with door monitoring contact

- ▶ Actuating head made of metal
- ▶ Auxiliary release on the front
- ▶ With door monitoring contact



Description

Approach direction



Figure

Horizontal and vertical

Can be adjusted in 90° steps

Solenoid operating voltage

- ▶ AC/DC 24 V +10%, -15%

Guard locking type

STP4 Open-circuit current principle, guard locking by applying voltage to the guard locking solenoid. Release by spring force.


Switching element

4141 Slow-action switching contact 2 NC (→) + 2 NC (←) (door monitoring contacts)

Auxiliary release

Is used for releasing the guard locking with the aid of a tool. To protect against tampering, the auxiliary release is sealed with sealing lacquer.


Dimension drawing





1 Auxiliary release

2 Locking screw


4141



 Solenoid monitoring

 Door monitoring

Switching functions



Technical data

Approvals



Mechanical values and environment

Housing material	Housing	Reinforced thermoplastic
Weight	Net	0,5 kg
Ambient temperature		-20 ... 55 °C
Degree of protection		IP67
Mechanical life		1 x 10 ⁶
Contact material		Silver alloy, gold flashed
Switching principle		Slow-action switching contact
Installation orientation		Any
Number of door position positively driven contacts		2
Number of guard lock monitoring positively driven contacts		2
Connection	3 x	M20 x 1.5
Approach speed		max.20 m/min
Actuation frequency		max.1200 1/h
Guard locking principle		Open-circuit current principle
Locking force F _{max}		2500 N
Locking force F _{Zh}		2000 N
Retention force		20 N
Extraction force		30 N
Actuating force		35 N
Insertion depth		24,5 mm

Electrical connection ratings

Thermal rated current I _{th}		4 A
Utilization category acc. to EN 60947-5-1	AC-15	4A 230V
	DC-13	4A 24V
Solenoid operating voltage	AC/DC	24 V -15% ... +10%
Short circuit protection according to IEC 60269-1		4A gG
Rated insulation voltage U _i		250 V
Rated impulse withstand voltage U _{imp}		2,5 kV
Switching voltage	Min. at 10mA	12 V
Switching current	Min. at 24V	1 mA
Connection rating		8 W
Solenoid duty cycle		100 %
Connection cross-section		0,34 ... 1,5 mm ²

Reliability values according to EN ISO 13849-1

	Monitoring of guard locking and the safety guard position	
B10 _D		5 x 10 ⁶

In combination with Actuator BETAETIGER-S-GT-SN

Mechanical values and environment

Overtravel

5 mm

Accessories

Actuator

Actuator L, bent, for safety switches SGA/SGP/STA/STP/STM for insertion funnel



095741
BETAETIGER-S-WQT-LN

- ▶ Two safety screws included
 - ▶ Actuator with rubber bush
-



105809
BETAETIGER-S-WT-LN-C2115

- ▶ Two stainless safety screws per actuator
 - ▶ Actuator with rubber bush
 - ▶ Minimum door radius 300 mm
-

Actuator L for safety switches SGA/SGP/STA/STP/STM for insertion funnel



095739
BETAETIGER-S-GT-LN

- ▶ Two safety screws included
 - ▶ Actuator with rubber bush
-

Actuator S, bent, for safety switches SGA/SGP/STA/STP/STM



095740
BETAETIGER-S-WQT-SN

- ▶ Two safety screws included
-



115073
BETAETIGER-S-W-SN-C2115

- ▶ Two stainless safety screws per actuator
 - ▶ Minimum door radius 300 mm
-



105808
BETAETIGER-S-WT-SN-C2115

- ▶ Two stainless safety screws per actuator
 - ▶ Actuator with rubber bush
 - ▶ Minimum door radius 300 mm
-

Actuator S for safety switches SGA/SGP/STA/STP/STM



097861
BETAETIGER-S-G-SN-C2115

- ▶ Two safety screws included
 - ▶ Physically compatible with TP actuator P-G
-



095738
BETAETIGER-S-GT-SN

- ▶ Two safety screws included
- ▶ Actuator with rubber bush

Hinged actuator L left/right, for safety switches SGA/SGP/STA/STP/STM for insertion funnel



096844
RADIUSBETAETIGER-S-LR-LN

- ▶ Actuators made of stainless steel
- ▶ Two stainless safety screws per actuator
- ▶ For doors hinged on the right or left

Hinged actuator L top/bottom, for safety switches SGA/SGP/STA/STP/STM for insertion funnel



096697
RADIUSBETAETIGER-S-OU-LN

- ▶ Actuators made of stainless steel
- ▶ Two stainless safety screws per actuator
- ▶ For doors hinged at top and bottom

Hinged actuator S left/right for safety switches SGA/SGP/STA/STP/STM



096838
RADIUSBETAETIGER-S-LR-SN

- ▶ Actuators made of stainless steel
- ▶ Two safety screws included
- ▶ For doors hinged on the right or left

Hinged actuator S top/bottom for safety switches SGA/SGP/STA/STP/STM



095315
RADIUSBETAETIGER-S-OU-SN

- ▶ Actuators made of stainless steel
- ▶ Two safety screws included
- ▶ For doors hinged at top and bottom

Bolt

Bolt BTC-ST/G... without escape release for safety switches STA, STP, SGP and SGA



106284
BTC-ST/G-S-TH-00-X

- ▶ Aluminum bolt
- ▶ For doors hinged on the left or right
- ▶ Can be locked in open position with padlocks
- ▶ Actuator included

Bolt BTM-UNIP-S... for safety switches TP, STP, STA and CTP



159951
BTM-UNIP-S-TH-00-X-159951

- ▶ Steel bolt
- ▶ For doors hinged on the left or right
- ▶ Can be locked in open position with padlocks
- ▶ Actuator not included

Bolt S... for safety switches STA, STP, SGP and SGA



096384
RIEGEL S-A

- ▶ Steel bolt
- ▶ For doors hinged on the right
- ▶ Can be locked in open position with padlocks
- ▶ Actuator included



096385
RIEGEL S-C

- ▶ Steel bolt
- ▶ For doors hinged on the left
- ▶ Can be locked in open position with padlocks
- ▶ Actuator included

Bolt STP-GFK for safety switches STA, STP, SGP and SGA



098121
RIEGEL STP-GFK

- ▶ Fiber glass reinforced plastic bolt
- ▶ For doors hinged on the left or right
- ▶ Can be locked in open position with padlocks
- ▶ Actuator included

Connection material


Cable glands M20x1.5, cable Ø 6-12 mm



086233
EKPM20/06 086233

Function expansion

Built-in LED, light shines to front



095510
EINBAULEUCHTE LED-F M20X1,5

Built in LED, light shines to side

Built-in LED, light shines to side



087423
EINBAULEUCHTE LED M20X1,5

Emergency unlocking for safety switches CTP/TP/STP



099877
NOTENTSPERRUNG TP/STP

Handle for wire front release



099795
AY-HDL-099795


- ▶ Suitable for all wire front releases

Insertion funnel for safety switches SGP/STA/STP/STM/SGA



093157
EINFUEHRTRICHTER-S

LED set



098035
STP LED SET

Lock for auxiliary release for safety switches CTP/TP/STP



084177
SCHLOSS TP
VERSCHIEDENSCHLIESSEND

- ▶ Lock unique locking
- ▶ Key removable in "unlocked" and "locked" positions



086236
SCHLOSS TP GLEICHSCHLIESSEND

- ▶ Identical locking
- ▶ Key removable in "unlocked" and "locked" positions



109212
SCHLOSS TP GLEICHSCHLIESSEND
C2293

- ▶ Identical locking
- ▶ Key can be removed only in "unlocked" position



121917
SCHLOSS TP GLEICHSCHLIESSEND
C2416

- ▶ Identical locking
- ▶ Key removable in "locked" position

Lockout bar STA/STP/SGA/SGP/STM



105701
SPERREINSATZ STP/STA

- ▶ Prevents unintentional closing of the door
- ▶ Can be secured with padlocks

Release with automatic reset for safety switches CTP/TP/STP



103110
ENTRIEGELUNG RUECKSTELLEND
TP/STP

Wire front release



096230
AE-B-A1-02,0-096230

- ▶ Can be used as escape release or emergency release
- ▶ No automatic return
- ▶ Sheath length 2 m (rope length 6 m)



097747
AE-B-A1-02,0-F-097747

- ▶ Can be used as escape release or emergency release
- ▶ Automatic return
- ▶ Sheath length 2 m (rope length 6 m)



098313
AE-B-A1-03,0-098313

- ▶ Can be used as escape release or emergency release
- ▶ No automatic return
- ▶ Sheath length 3 m (rope length 6 m)



111233
AE-B-A1-03,0-F-111233

- ▶ Can be used as escape release or emergency release
- ▶ Automatic return
- ▶ Sheath length 3 m (rope length 6 m)



098314
AE-B-A1-04,0-098314

- ▶ Can be used as escape release or emergency release
- ▶ No automatic return
- ▶ Sheath length 4 m (rope length 6 m)



124770
AE-B-A1-06,0-F-124770

- ▶ Can be used as escape release or emergency release
- ▶ Automatic return
- ▶ Rope length 6 m (without sheath)



125582
AE-B-A1-06,0-125582

- ▶ Can be used as escape release or emergency release
- ▶ No automatic return
- ▶ Rope length 6 m (without sheath)

Mounting accessories

Mounting plates EMP-B1 for actuators for safety switches CTP, TP...A, STA, STP, TX and TZ



093457
EMP-B1

Mounting plates EMP-B2 for actuators for safety switches CTP, TP...A, STA, STP, TX and TZ



093458
EMP-B2

Mounting plates EMP-SB for safety switches CTP, TP...A, STA, STP and TX



093456
EMP-SB

- ▶ For vertical and horizontal mounting of safety switches TP...A, STA, STP and TX

Switch bracket CTP/TP/STP GFK



096613
SCHALTERAUFNAHME TP/STP GFK

- ▶ Switch bracket made of fiber glass reinforced plastic
- ▶ For doors hinged on the left or right

Spare parts

Replacement key for mechanical key release



099434
ERSATZSCHLUESSEL
GLEICHSCHL0354

Contacts

🏠 EUCHNER GmbH + Co. KG
Kohlhammerstraße 16
70771 Leinfelden-Echterdingen

☎ +49 711 7597-0

📠 +49 711 753316

✉ [info\(at\)euchner.de](mailto:info(at)euchner.de)