

► Model SLM100

LED

StreamLine® Modular Multifunctional LED Beacon

Multiple input technology allows steady, flashing or rotating light effects.



Model SLM100 shown with mounting base options (ordered separately)

A B C G R

Model SLM100 offers a multifunctional LED beacon with high optical performance. Developed with a multiple input technology, Model SLM100 allows three separate light effects (steady, flashing or rotating) controllable via independent electric contacts.

The steady light option offers a conspicuous and consistent light signal. The flashing mode consists of a triple-flash strobe effect ideal for all applications where an immediate attention gain is mandatory. And, the rotating light offers a traditional rotating beacon effect without moving parts, which enhances product life.

Model SLM100 body material is a self extinguishing polycarbonate material with high impact and UV resistance suitable for outdoor applications.

FEATURES

- Compatible with 12-24VAC/DC or 120-240VAC*
- PLC compatible with PNP or NPN connections*
- Three separate inputs: steady, flashing or rotating
- 100,000 hour LED
- Five color options

- Five mounting base options
- Type 4X, IP66
- CE Compliant
- UL and cUL listed

* Voltage and PLC connections are dependent on selected base.

MODEL	VOLTAGE	FLASH RATE/MINUTE	ROUND PER MINUTE
SLM100 *	12-24VAC/DC or 120-240VAC	85 (+/-10)	140 (+/-10)

* Indicates color: (A) Amber, (B) Blue, (C) Clear, (G) Green or (R) Red

MAXIMUM OPERATING CURRENT (mA)					
12 VDC	24 VDC	12 VAC	24 VAC	120 VAC	240 VAC
300	150	510	360	100	70

StreamLine® Modular Multifunctional LED Beacon (SLM100)

SPECIFICATIONS

Lamp Life:	100,000 Hours	100,000 Hours
Light Source:	LED Array	LED Array
Operating Temperature:	-22°F to 122°F	-30°C to 50°C
Weight (unit(s) + base = total weight)		
SLM100	7.05 oz.	0.20 kg
Shallow Base	2.12 oz.	0.06 kg
Deep Base		
12-24 VDC/AC	4.23 oz.	0.12 kg
120-240 VAC	6.0 oz.	0.17kg
Wall Mount		
12-24 VDC/AC	6.70 oz.	0.19 kg
120-240 VAC	8.47 oz.	0.24 kg
Pipe Mount		
12-24 VDC/AC	5.29 oz.	0.15 kg
120-240 VAC	6.70 oz.	0.19 kg
Twin Wall Mount		
12-24 VDC/AC	9.17 oz.	0.26 kg
120-240 VAC	12.35 oz.	0.35 kg

HOW TO ORDER

- Specify model number SLM100 and color
- Specify required mounting base (see chart)
- Optional dome guard
For shallow mounting base (SLMDG3)
For deep mounting base (SLMDG4)
- Accessories for Twin and Wall Mount Bases
Cable Gland, M20, Gray, 2 Pack (K77700416)
Cable Gland, M20, Red, 2 Pack (K77700416-01)
- Accessories for Pipe Mount Base
1" NPT Adapter (SLMNPT1)
1/2" NPT Adapter (SLMNPT2)



MOUNTING BASE OPTIONS

	Shallow Base	Model Number	Base Color	Voltage	
		SLMBS-012-024GY	Gray	12-24VDC/AC	
	Deep Base	SLMBD-012-024GY	Gray	12-24VDC/AC	
		SLMBD-PNP-012-024GY	Gray	12-24VDC/AC	
		SLMBD-012-024R	Red	12-24VDC/AC	
		SLMBD-120-240GY	Gray	120-240VAC	
		SLMBD-120-240R	Red	120-240VAC	
	Wall Mount	SLMBW-012-024GY	Gray	12-24VDC/AC	
		SLMBW-PNP-012-024GY	Gray	12-24VDC/AC	
		SLMBW-120-240GY	Gray	120-240VAC	
	Pipe Mount	SLMBP-012-024GY	Gray	12-24VDC/AC	
		SLMBP-PNP-012-024GY	Gray	12-24VDC/AC	
		SLMBP-120-240GY	Gray	120-240VAC	
	Twin Wall Mount	SLMBT-012-024GY	Gray	12-24VDC/AC	
		SLMBT-PNP-012-024GY	Gray	12-24VDC/AC	
		SLMBT-120-240GY	Gray	120-240VAC	