



ARCA AR 884

8 x 8

UL Type 4, 4X, 6, 6P, 12 and 13

Including: 10-32 brass inserts, cover with formed in place PUR gasket. Enclosure mounting foot kit. 10-32 screws for panel mounting. Screw cover versions with 4 stainless cover screws. Hinged screw cover versions with stainless hinge pin and 2 cover screws. Hinged cover versions with latched cover and stainless hinge pin. Quick release latches. (Latch options available.)

Enclosures

Order symbol	Dimensions inch	Dimensions mm	Description
AR884SC	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Opaque screw cover
AR884CHSC	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged opaque screw cover
AR884CHL	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged opaque cover w/Plastic quick release latch
AR884CHSSL	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged opaque cover w/S.S. Lockable latch
AR884CHSS	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged opaque cover w/S.S. Quick release latch
AR884CHTSS	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged opaque cover w/S.S. Lockable twist latch
AR884SCT	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Transparent screw cover
AR884CHSCT	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged transparent screw cover
AR884CHLT	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged transparent cover w/Plastic quick release latch
AR884CHSSLT	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged transparent cover w/S.S. Lockable latch
AR884CHSST	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged transparent cover w/S.S. Quick release latch
AR884CHTSST	8 x 8 x 4	203 x 203 x 102	PC Enclosure • Hinged transparent cover w/S.S. Lockable twist latch

Accessories

Order symbol	Dimensions inch	Dimensions mm	Description
APBP88	6.9 x 6.9	175 x 175	PVC Back Panel
ABP88	6.9 x 6.9	175 x 175	Painted Steel Back Panel
ALBP88	6.9 x 6.9	175 x 175	Aluminum Back Panel
ADFP88	6.9 x 6.9	175 x 175	Dead Front Panel w/ screws
ASPK88			Hinged Panel Kit incl. AL Panel
ASPHK8			Hinged Panel Kit w/o Panel
AMFL8			Mounting Flange Set for 8" Wide Enclosure

