

CAB PC/ABS 3030

300 x 300

PC: IP 65, IK 08
ABS: IP 65, IK 08

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs. 3B-versions: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.



Enclosures

Order symbol	Code	Dimensions	Description
CAB PC 303018 G	8113340	300 x 300 x 180	Cabinet, PC, Grey door ▪ Latches on the long side
CAB PC 303018 G3B	8113342	300 x 300 x 180	Cabinet, PC, Grey door ▪ Lock on the long side
CAB PC 303018 T	8113040	300 x 300 x 180	Cabinet, PC, Smoked transparent door ▪ Latches on the long side
CAB PC 303018 T3B	8113042	300 x 300 x 180	Cabinet, PC, Smoked transparent door ▪ Lock on the long side
CAB ABS 303018 G	8183340	300 x 300 x 180	Cabinet, ABS, Grey door ▪ Latches on the long side
CAB ABS 303018 G3B	8183342	300 x 300 x 180	Cabinet, ABS, Grey door ▪ Lock on the long side
CAB ABS 303018 T	8183040	300 x 300 x 180	Cabinet, ABS, Smoked transparent door ▪ Latches on the long side
CAB ABS 303018 T3B	8183042	300 x 300 x 180	Cabinet, ABS, Smoked transparent door ▪ Lock on the long side

Accessories

Order symbol	Code	Dimensions	Description
EKIV 33	4712118	270 x 270	Mounting plate
EKIV 27	4712127	35 x 266	DIN-35 Mounting rail
DS35270E1	2551270	35 x 270 x 7	DIN-35 Mounting rail
FP A 33	8392227	266 x 268	Swing-out door/Front plate (aluminium)
MB 12225 AL	8390007		Swing door set ▪ for aluminium front plates
FP 33	8392305	276 x 268	Front plate ▪ Black
FP 12-33	8392219	278 x 278	Front plate ▪ 12 modules
FP 12x2-33	8392220	278 x 278	Front plate ▪ 2x12 modules
DRF 33	4712205		DIN rail frame set ▪ incl. a pair of metal profile bar, mounting screws and front plate holders

