



CAB PC 3040

15.7 x 11.8

UL Type 1, 4, 4X, 12 and 13

Including: Cabinet base, door with EPDM gasket, latches, hardware screws for accessory mounting and corner plugs. 3B-versions: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, hardware screws for accessory mounting and corner plugs.

Enclosures

Order symbol	UL Order symbol	Dimensions inch	Dimensions mm	Description
CAB PC 304018 G	UL CAB PC 304018 G	15.7 x 11.8 x 7.1	400 x 300 x 180	Opaque door ▪ Latches short side
CAB PC 403018 G	UL CAB PC 403018 G	15.7 x 11.8 x 7.1	400 x 300 x 180	Opaque door ▪ Latches long side
CAB PC 403018 G3B	UL CAB PC 403018 G3B	15.7 x 11.8 x 7.1	400 x 300 x 180	Opaque door ▪ Locks long side
CAB PC 304018 T	UL CAB PC 304018 T	15.7 x 11.8 x 7.1	400 x 300 x 180	Smoked transparent door ▪ Latches short side
CAB PC 403018 T	UL CAB PC 403018 T	15.7 x 11.8 x 7.1	400 x 300 x 180	Smoked transparent door ▪ Latches long side
CAB PC 403018 T3B	UL CAB PC 403018 T3B	15.7 x 11.8 x 7.1	400 x 300 x 180	Smoked transparent door ▪ Locks long side

Accessories

Order symbol	Dimensions inch	Dimensions mm	Description
EKIV 43	14.6 x 10.6	370 x 270	Back Panel
EKIV 27	1.4 x 10.5	35 x 266	DIN-35 Mounting rail
EKIV 37	1.4 x 14.4	35 x 366	DIN-35 Mounting rail
FP A 43	10.5 x 14.5	266 x 368	Swing-out door/Front panel (aluminum)
MB 12225 AL			Swing door kit ▪ for aluminum front panels
DRF 43/44			DIN rail frame kit ▪ incl. a pair of metal profile bar, mounting screws and front panel holders

