



# EURONORD PC/ABS 1224

244 x 124 PC: IP 66/IP 67, IK 07/IK 08  
ABS: IP 66/IP 67, IK 07

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and ferrous stainless steel cover screws. Q-versions: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and quick-locking cover screws.

## Enclosures

Order symbol	Code	Dimensions	Description
PC 122410	7032780	244 x 124 x 102	Enclosure, PC • Grey cover
PCT 122410	7022781	244 x 124 x 102	Enclosure, PC • Transparent cover
PCQ 122410	7033781	244 x 124 x 102	Enclosure, PC, IP 65 • Grey cover (quick-locking)
PCTQ 122410	7022780	244 x 124 x 102	Enclosure, PC, IP 65 • Transparent cover (quick-locking)
AB 122410	7083780	244 x 124 x 102	Enclosure, ABS • Grey cover
ABQ 122410	7083781	244 x 124 x 102	Enclosure, ABS, IP 65 • Grey cover (quick-locking)

## Accessories

Order symbol	Code	Dimensions	Description
TM 1224	9512016	214 x 111	Mounting plate
TRM 0812	9820009	15 x 106	DIN-15 Mounting rail
MIN 20	6314578	15 x 225	DIN-15 Mounting rail
TRH 1212	9822002	35 x 110	DIN-35 Mounting rail
TRH 24	9822008	35 x 226	DIN-35 Mounting rail
TF 28037	7028337		Wall fastening lug (4 pcs) • incl. screws
TH A	9802001		Grey plastic hinges (2 pcs) • incl. mounting screws

