

CARDMASTER PC 30/25

12.6 x 10.2

NEMA 1, 4X* and 12K

*PC 17/16L, 17/16 and 21/18: -3 and -FC3 -models



Including: Base, terminal compartment cover with gasket and hardware screws for accessory mounting. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Opaque screw cover with PUR gasket and cover screws.

Enclosures

Order symbol	Dimensions inch	Dimensions mm	Description
PC 30/25-3	12.6 x 10.2 x 5.1	320 x 260 x 129	Smoked transparent hinged cover
PC 30/25-FC3	12.4 x 10.2 x 4.3	314 x 260 x 110	Opaque screw cover
PC 30/25-3 USA	12.6 x 10.2 x 5.1	320 x 260 x 129	0.85" knock-outs, AL front panel

Accessories

Order symbol	Dimensions inch	Dimensions mm	Description
MP 30/25	11.1 x 8.5	282 x 215	Back Panel
FP 30/25	11.4 x 7.4	289 x 189	Front panel (aluminum)

