



MNX PCM 100

130 x 80

PC: IP 66/IP 67, IK 08

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Enclosures

| Order symbol | Code | Dimensions | Description |
|---------------|---------|----------------|--|
| PCM 100/60 G | 6016301 | 130 x 80 x 60 | Enclosure, PC • Grey cover |
| PCM 100/75 G | 6016302 | 130 x 80 x 75 | Enclosure, PC • Grey cover |
| PCM 100/100 G | 6016303 | 130 x 80 x 100 | Enclosure, PC • Grey cover |
| PCM 100/125 G | 6016304 | 130 x 80 x 125 | Enclosure, PC • Grey cover |
| PCM 100/60 T | 6016901 | 130 x 80 x 60 | Enclosure, PC • Smoked transparent cover |
| PCM 100/75 T | 6016902 | 130 x 80 x 75 | Enclosure, PC • Smoked transparent cover |
| PCM 100/100 T | 6016903 | 130 x 80 x 100 | Enclosure, PC • Smoked transparent cover |
| PCM 100/125 T | 6016904 | 130 x 80 x 125 | Enclosure, PC • Smoked transparent cover |

Accessories

| Order symbol | Code | Dimensions | Description |
|--------------|---------|------------|--|
| MIV 100 | 5514076 | 98 x 48 | Mounting plate (Galvanized steel) |
| MIN 5 | 6314575 | 15 x 50 | DIN-15 Mounting rail |
| MIN 10 | 6314576 | 15 x 100 | DIN-15 Mounting rail |
| MIV 5 | 5514081 | 35 x 50 | DIN-35 Mounting rail |
| MIV 10 | 5514082 | 35 x 100 | DIN-35 Mounting rail |
| FP A 100/130 | 6314570 | 120 x 62 | Front plate (Aluminium) |
| HFP 130 | 6314563 | | Front plate hinge series for FP A 100-125 • (2 pcs) incl. screws |
| FP 22046 | 8522346 | | Wall fastening lug (4 pcs) • incl. screws |

