

# MNX PCM 200

255 x 180

PC: IP 66/IP 67, IK 08



Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

## Enclosures

Order symbol	Code	Dimensions	Description
PCM 200/63 G	6016324	255 x 180 x 63	Enclosure, PC ▪ Grey cover
PCM 200/75 G	6016326	255 x 180 x 75	Enclosure, PC ▪ Grey cover
PCM 200/100 G	6016327	255 x 180 x 100	Enclosure, PC ▪ Grey cover
PCM 200/150 G	6016329	255 x 180 x 150	Enclosure, PC ▪ Grey cover
PCM 200/63 T	6016924	255 x 180 x 63	Enclosure, PC ▪ Smoked transparent cover
PCM 200/75 T	6016926	255 x 180 x 75	Enclosure, PC ▪ Smoked transparent cover
PCM 200/100 T	6016927	255 x 180 x 100	Enclosure, PC ▪ Smoked transparent cover
PCM 200/150 T	6016929	255 x 180 x 150	Enclosure, PC ▪ Smoked transparent cover

## Accessories

Order symbol	Code	Dimensions	Description
MIV 200	5514080	223 x 148	Mounting plate (Galvanized steel)
MIN 15	6314577	15 x 150	DIN-15 Mounting rail
MIN 20	6314578	15 x 225	DIN-15 Mounting rail
MIV 15	5514083	35 x 150	DIN-35 Mounting rail
MIV 20	5514084	35 x 225	DIN-35 Mounting rail
FP A 200/180	6314574	237 x 170	Front plate (Aluminium)
HFP 180	6314564		Front plate hinge series for FP A 150-200 ▪ (2 pcs) incl. screws
FP 22046	8522346		Wall fastening lug (4 pcs) ▪ incl. screws

