

SOLID PC/ABS 1919

188 x 188 PC: IP 66/IP 67, IK 08/IK 09
ABS: IP 66/IP 67, IK 08

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.



Enclosures

Order symbol	Code	Dimensions	Description
PC 1919 13 G	5330359	188 x 188 x 130	Enclosure, PC • Grey cover
PC 1919 18 G	5330369	188 x 188 x 180	Enclosure, PC • Grey cover
PC 1919 13 G-2FSH	2539505	188 x 188 x 130	Enclosure, PC, IP 65 • Grey hinged cover
PC 1919 18 G-2FSH	2539507	188 x 188 x 180	Enclosure, PC, IP 65 • Grey hinged cover
PC 1919 13 T	5330059	188 x 188 x 130	Enclosure, PC • Transparent cover
PC 1919 18 T	5330069	188 x 188 x 180	Enclosure, PC • Transparent cover
PC 1919 13 T-2FSH	2539535	188 x 188 x 130	Enclosure, PC, IP 65 • Transparent hinged cover
PC 1919 18 T-2FSH	2539537	188 x 188 x 180	Enclosure, PC, IP 65 • Transparent hinged cover
ABS 1919 13 G	5880359	188 x 188 x 130	Enclosure, ABS • Grey cover
ABS 1919 18 G	5880369	188 x 188 x 180	Enclosure, ABS • Grey cover
ABS 1919 13 G-2FSH	9880401	188 x 188 x 130	Enclosure, ABS, IP 65 • Grey hinged cover
ABS 1919 18 G-2FSH	9880405	188 x 188 x 180	Enclosure, ABS, IP 65 • Grey hinged cover
ABS 1919 13 T	5880059	188 x 188 x 130	Enclosure, ABS • Transparent cover
ABS 1919 18 T	5880069	188 x 188 x 180	Enclosure, ABS • Transparent cover
ABS 1919 13 T-2FSH	9880451	188 x 188 x 130	Enclosure, ABS, IP 65 • Transparent hinged cover
ABS 1919 18 T-2FSH	9880455	188 x 188 x 180	Enclosure, ABS, IP 65 • Transparent hinged cover

Accessories

Order symbol	Code	Dimensions	Description
EKHVT	3770548	148 x 148	Mounting plate
EKV 12	3770647	35 x 160	DIN-35 Mounting rail

