



SOLID PC/ABS 5628

22.0 x 10.9 PC: UL Type 1, 3, 3S, 4, 4X, 6, 6P and 12
ABS: NEMA 1, 3, 3S, 4, 4X, 6, 6P and 12

Including: Base with hardware screws for accessory mounting, cover with PUR gasket and polyamide cover screws.

Enclosures

Order symbol	UL Order symbol	Dimensions inch	Dimensions mm	Description
PC 5628 13 G	UL PC 5628 13 G	22 x 10.9 x 5.1	558 x 278 x 130	Enclosure, PC • Opaque cover
PC 5628 13 G-3FSH	UL PC 5628 13 G-3FSH	22 x 10.9 x 5.1	558 x 278 x 130	Enclosure, PC, IP 65 • Opaque hinged cover
PC 5628 13 T	UL PC 5628 13 T	22 x 10.9 x 5.1	558 x 278 x 130	Enclosure, PC • Transparent cover
PC 5628 13 T-3FSH	UL PC 5628 13 T-3FSH	22 x 10.9 x 5.1	558 x 278 x 130	Enclosure, PC, IP 65 • Trans. hinged cover
ABS 5628 13 G		22 x 10.9 x 5.1	558 x 278 x 130	Enclosure, ABS • Opaque cover

Accessories

Order symbol	Dimensions inch	Dimensions mm	Description
EKTVT	20.4 x 9.4	518 x 238	Back Panel
EKV 22	1.4 x 9.3	35 x 235	DIN-35 Mounting rail
EKV 50	1.4 x 19.7	35 x 500	DIN-35 Mounting rail
EKTZR	22 x 10.9 x 2	558 x 278 x 50	Extension frame

