

MNX PCM 95

3.9 x 3.9

UL Type 1, 4, 4X and 6



Including: Base with metric knock-outs and PUR gasket, cover with polyamide cover screws, and hardware screws for accessory mounting.

Enclosures

Order symbol	UL Order symbol	Dimensions inch	Dimensions mm	Description
PCM 95/60 G	UL PCM 95/60 G	3.9 x 3.9 x 2.4	100 x 100 x 60	Enclosure, PC ▪ Opaque cover
PCM 95/75 G	UL PCM 95/75 G	3.9 x 3.9 x 3	100 x 100 x 75	Enclosure, PC ▪ Opaque cover
PCM 95/60 T	UL PCM 95/60 T	3.9 x 3.9 x 2.4	100 x 100 x 60	Enclosure, PC ▪ Smoked transparent cover
PCM 95/75 T	UL PCM 95/75 T	3.9 x 3.9 x 3	100 x 100 x 75	Enclosure, PC ▪ Smoked transparent cover

Accessories

Order symbol	Dimensions inch	Dimensions mm	Description
MIV 95	2.6 x 3.1	66 x 80	Back Panel (Galvanized steel)
B-3	1.4 x 3.1	35 x 80	DIN-35 Mounting rail
FP 22046			Mounting foot kit (4 pcs) ▪ incl. screws

