

## TECHNICAL DATA

# Fluke 700PTPK Pneumatic Test Pressure Kit



## Key features

- Easy to use, rugged and reliable construction, capable of generating pneumatic pressure from -12.7 psi/ -0.87 bar to 600 psi/41 bar
- Combine with one of the Fluke 700G Precision Pressure Gauges for a complete pressure testing and calibration solution
- In addition, combine with the Fluke 700G/TRACK Software to upload over 8,000 pressure measurements logged in the field to a PC

## Product overview: Fluke 700PTPK Pneumatic Test Pressure Kit

Generates pressure up to 600 psi, 41 bar. Includes the 700PTP-1 pneumatic hand pump, test hoses and adapters, and protective hard case.

## Ordering information



### **Fluke 700PTK**

Fluke 700PTK Pneumatic Test Pressure Kit

---

Pneumatic Test Pressure Kit with Pneumatic Hand Pump

Includes:

- 1 hose kit and adapters
  - Hard case
-

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2022 Fluke Corporation.  
Specifications subject to change without notice.  
09/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**