

TECHNICAL DATA

Fluke 80PK-18 Pipe Clamp Temperature Probe Kit



Key features

- Type-K thermocouple for fast temperature and superheat measurements of pipe surfaces
- For pipe diameters:
 - 6.4 mm to 64 mm (0.25 in to 2.5 in)
 - 80PK-8 - 6.4 mm to 34.9 mm (0.25 in to 1.375 in)
 - 80PK-10 - 32 mm to 64 mm (1.25 in to 2.5 in)
- Measurement range: -29 °C to 149 °C (-20 °F to 300 °F)
- Measurements are repeatable to 0.56 °C (1 °F)
- Durable ribbon sensor
- 1 m (39 in) lead
- One year warranty

Product overview: Fluke 80PK-18 Pipe Clamp Temperature Probe Kit

The 80PK-18 Pipe Clamp Temperature Probe kit combines the standard 80PK-8 pipe clamp with the larger sized 80PK-10 pipe clamp, to give you a full range of measurement sizes. The Type K, thermocouples clamp securely to pipes for fast temperature and superheat measurement. The included soft carrying case allows you to conveniently keep both clamps close by for any situation.

Ordering information



Fluke 80PK-18

Fluke. *Keeping your world up and running.®*

Fluke Europe B.V.

P.O. Box 1186
5602 BD Eindhoven
The Netherlands
www.fluke.com/en

©2022 Fluke Corporation. All rights reserved.
Data subject to alteration without notice.
09/2022

For more information call:

In Middle East/Africa
+31 (0)40 267 5100

**Modification of this document is not permitted
without written permission from Fluke Corporation.**