

TECHNICAL DATA

Fluke VPS101 – Voltage Probe Set, 1:1, one black



Key features

- 300 V CAT III rated
 - 1:1 Voltage Probe
 - Hook Clip for Probe Tip
 - Ground Lead with Mini Alligator
 - Insulation Sleeve
- 30 V CAT II rated Ground Spring for Probe Tip

Product overview: Fluke VPS101 – Voltage Probe Set, 1:1, one black

Double insulated voltage probe for ScopeMeter 190 series.

Specifications: Fluke VPS101 – Voltage Probe Set, 1:1, one black

Specification	
Attenuation	1x
Bandwidth	30 MHz
Max. input voltage	300 V CAT III
Max. voltage to ground	600 V CAT III per IEC / EN61010-031

Input resistance	1 MΩ
Input capacitance	42 pF + input capacitance of instrument
Cable length	1.2 m
Warranty	One year

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2022 Fluke Corporation.
Specifications subject to change without notice.
09/2022

**Modification of this document is not permitted
without written permission from Fluke Corporation.**