

TECHNICAL DATA

## VPS212-G - Voltage Probe Set, 10:1, one grey



### Product overview: VPS212-G - Voltage Probe Set, 10:1, one grey

**Double insulated voltage probe for ScopeMeter 190 series.**

Each probe set includes:

- 600 V CAT III / 1000 V CAT II rated 10:1 Voltage Probe
- Hook Clip for Probe Tip
- Ground Lead with Mini Alligator
- Insulation Sleeve
- 30 V CAT II rated Ground Spring for Probe Tip

Specification:

- Attenuation: 10x
- Bandwidth: 200 MHz
- Max. Input Voltage 1000 V CAT II or 600 V CAT III
- Max. Voltage to ground: 1000 V CAT II or 600 V CAT III per IEC / EN61010-031
- Input Resistance: 10 M $\Omega$
- Input Capacitance: 18 pF
- Compensation range: 10 to 30 pF
- Cable Length: 2.5 m

## Specifications: VPS212-G - Voltage Probe Set, 10:1, one grey

Specification	
Attenuation	10x
Bandwidth	200 MHz
Max. input voltage	1000 V CAT II or 600 V CAT III
Max. voltage to ground	1000 V CAT II or 600 V CAT III per IEC / EN61010-031
Input resistance	10 M $\Omega$
Input capacitance	18 pF
Compensation range	10 to 30 pF
Cable length	2.5 m

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2022 Fluke Corporation.  
Specifications subject to change without notice.  
09/2022

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**