

IEC Power Devices
IEC Contactors
C-2000
Nonreversing
AC/DC Controlled, 4-Pole
 HP Ratings AC-3 Duty

125-500 Hp (460V) Standard Terminals

Maximum Current @ 460 V (A) AC-3	3-Phase HP @60 Hz, 200V	3-Phase HP @60 Hz, 230V	3-Phase HP @60 Hz, 460V	3-Phase HP @60 Hz, 575V	Auxiliary Contacts ²	Contact Configuration	Product Number ¹
156A	50	60	125	125	1NO-1NC	4NO	CK08BE411†
192A	60	75	150	150	1NO-1NC	4NO	CK09BE411†
302A	100	100	250	300	1NO-1NC	4NO	CK95BE411†
398A	125	150	300	400	1NO-1NC	4NO	CK10CE411†
398A	125	150	300	400	1NO-1NC	4NO	CK10BE411†
480A	150	200	400	500	1NO-1NC	4NO	CK11CE411†
480A	150	200	400	500	1NO-1NC	4NO	CK11BE411†
602A	200	250	500	600	1NO-1NC	4NO	CK12BE411†

¹To complete the contactor product number, replace the †, in the product number with the appropriate digit from the Coil Selection table.

²Auxiliary contact shipped unassembled.

(Replace dagger (†) in product number with appropriate digit from table below.)

Coil Selection Table

AC 60/50 Hz	DC	†Coil Suffix
24-28	24-28	D
42-48	42-48	F
110-127	110-127	J
220-250	220-250	N
380-415	380-415	U
440-500	440-500	Y

