



 PRODUCT-DETAILS

P9PDNV0-AA

P9PDNV0-AA Lamp Block



360°

General Information

Extended Product Type:	P9PDNV0-AA
Product ID:	1SFA215831R1000
EAN:	7320500522936
Catalog Description:	P9PDNV0-AA Lamp Block
Long Description:	<p>The P9PDNV0-AA Lamp Block is: Modular metal - Lamp Block - Brown - Illuminated - Front mounting - 380 V</p> <p>This Lamp Block is part of ABB's modular metal range designed for mining, construction and heavy industry applications, combining the highest reliability with the full flexibility of a modular range.</p>
Display Name:	P9PDNV0-AA

Ordering

Minimum Order Quantity:	200 piece
Customs Tariff Number:	8536619090

Popular Downloads

Data Sheet, Technical Information:	1SFC151007C02__
Instructions and Manuals:	1SFC151011M0201

Dimensions

Product Net Width:	9.8 mm
Product Net Height:	39.5 mm
Product Net Depth / Length:	36.2 mm
Product Net Weight:	0.063 kg

Technical

Ambient Air Temperature:	Operation -30 ... 70 °C Storage -40 ... +70 °C
Color:	Brown
Illumination:	Illuminated
Lamp Type:	Lamp block for Ba9s socket for max 2W 380 V AC/DC LED
Mounting Type:	Front mounting
Rated Frequency (f):	50 / 60 Hz
Rated Operational Voltage:	Maximum 380 V
Connecting Capacity:	Flexible with Ferrule 1 x 0.75...2.5 mm ² Flexible with Ferrule 2 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 1 x 0.75...2.5 mm ² Flexible with Insulated Ferrule 2 x 0.75...2.5 mm ² Flexible 1 x 0.75 ... 2.5 mm ² Flexible 2 x 0.75 ... 2.5 mm ² Solid 1 x 0.75...2.5 mm ² Solid 2 x 0.75...2.5 mm ²
Connection Type:	Screw Clamp
Terminal Type:	Screw Terminals
Tightening Torque:	0.9 N·m
Wire Stripping Length:	8 mm

Technical UL/CSA

Connecting Capacity UL/CSA:	1x 18...14 AWG 2x 18...14 AWG
------------------------------------	----------------------------------

Environmental

Degree of Protection:	Terminals IP20
------------------------------	----------------

Material Compliance

Conflict Minerals Reporting Template (CMRT):	9AKK108467A5658
REACH Declaration:	2CMT2022-006479
RoHS Declaration:	2CMT2022-006498
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA:	2CMT2023-006523
WEEE B2C / B2B:	Business To Business
WEEE Category:	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations

BV Certificate:	2CMT2019-005867
CB Certificate:	2CMT2019-005874
CQC Certificate:	CQC2013010304650811
CSA Certificate:	2CMT2019-005868
cULus Certificate:	2CMT2019-005868
Declaration of Conformity - CCC:	2020980304001860
Declaration of Conformity - CE:	2CMT2019-005862
Declaration of Conformity - UKCA:	2CMT2020-006121
DNV GL Certificate:	2CMT2019-005876
RINA Certificate:	2CMT2019-005866
UL Certificate:	2CMT2019-005868

Container Information

Package Level 1 Units:	bag 200 piece
Package Level 1 Width:	200 mm
Package Level 1 Depth / Length:	50 mm
Package Level 1 Height:	600 mm
Package Level 1 Gross Weight:	12.6 kg
Package Level 1 EAN:	7320500519332

External Classifications and Standards

ETIM 7:	EC000204 - Lamp holder block for control circuit devices
ETIM 8:	EC000204 - Lamp holder block for control circuit devices
eClass:	V11.0 : 27371209
UNSPSC:	39122221
IDEA Granular Category Code (IGCC):	5219 >> Switch part or accessory

Categories

Products > Low Voltage Products and Systems > Control Products > Pilot Devices > Modular Metal Range P9M

