



 PRODUCT-DETAILS

AB553

N3R (55 in X 20 in) ENC



General Information

Global Commercial Alias:	AB553
Extended Product Type:	AB553
Product ID:	1TQR255000R0000
EAN:	783164000863
Catalog Description:	N3R (55 in X 20 in) ENC
Long Description:	ReliaGear lighting panelboards are factory assembled on rigid steel frames and equipped with circuit breakers from 15 A to 800 A. The maximum fully-rated short circuit rating is equal to 65 kAIC to 240 V AC and 480/277 V AC.
Display Name:	AB553

ABB EcoSolutions

ABB EcoSolutions:	Yes
End Of Life Disassembling Instructions:	1SQC173021M0202
Environmental Product Declaration - EPD:	1SQC173004D0201
Extended Product Lifetime:	Product Modularity
Recyclability Rate of the Product acc. to EN45555:	92.6 %

Installation

Instructions and Manuals: No document needed

Popular Downloads

Data Sheet, Technical Information: 9AKK107680A9334

Building Information Modeling – BIM: 1SQC173012D0201

Material Compliance

RoHS Information: No declaration needed

REACH Information: False - does not contain substances > 0.1 mass percentage

Ordering

Minimum Order Quantity: 1 piece

Dimensions

Product Net Width: 20.000 in

Product Net Height: 55.500 in

Product Net Depth / Length: 7.000 in

Product Net Weight: 90.000 lb

Container Information

Package Level 1 EAN: not available

Technical

Enclosure Type NEMA: Type3R

Surface Finishing: ANSI-61 grey polyester powder coat paint

Material: Steel

Certificates and Declarations

Declaration of Conformity - CE: No declaration needed

External Classifications and Standards

WEEE Category:	Product Not in WEEE Scope
UNSPSC:	39121321
eClass:	V11.1 : 27180101
IDEA Granular Category Code (IGCC):	4465 >> Enclosure General Accessories

Categories

Products > Low Voltage Products and Systems > NEMA Residential and Commercial Portfolio > Lighting Panels & Breakers > ReliaGear Lighting Panels

