



PRODUCT-DETAILS

308XT104A

308 Combo Starter-CR308XT104A Combination Motor Starter



360°

General Information

Global Commercial Alias:	308XT104A
Extended Product Type:	308 Combo Starter-CR308XT104A
Product ID:	7GSP021190R0006
Catalog Description:	308 Combo Starter-CR308XT104A Combination Motor Starter
Long Description:	Combination, Full-Voltage Motor Starter for single-speed induction motors for upto 400hp, 600V. Provide short Circuit protection by fuse, circuit breaker or MCP.
Display Name:	308XT104A

Material Compliance

REACH Declaration:	2CMT2021-006202
REACH Information:	False - does not contain substances > 0.1 mass percentage
Conflict Minerals Reporting Template (CMRT):	9AKK108467A5658
Toxic Substances Control Act - TSCA:	2CMT2023-006525

Ordering

Minimum Order Quantity:	1 EA
UPC:	783166390306

Dimensions

Product Net Width:	6.375 in
Product Net Height:	4.5 in
Product Net Depth / Length:	6.375 in
Product Net Weight:	3.64 lb

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	6.375 in
Package Level 1 Height:	6.375 in
Package Level 1 Depth / Length:	6.375 in
Package Level 1 Gross Weight:	3.64 lb

Technical

Number of Poles:	3P
------------------	----

Certificates and Declarations

cULus Certificate:	E1811
UL Certificate:	E1811

External Classifications and Standards

WEEE Category:	4. Large Equipment (Any External Dimension More Than 50 cm)
WEEE B2C / B2B:	Business To Business
CN8:	85365040
UNSPSC:	39121521
eClass:	V11.1 : 27371216

Categories

Products > Low Voltage Products and Systems > Control Products > Contactor Starters > NEMA Enclosed Starters



360°