



 PRODUCT-DETAILS

324CXDS

SIZE 1 SS OVERLOAD 0.8-1.7A-CR324CXDS Nema Overload Relay



360°

General Information

Global Commercial Alias:	324CXDS
Extended Product Type:	SIZE 1 SS OVERLOAD 0.8-1.7A-CR324CXDS
Product ID:	7GSP021460R0006
Catalog Description:	SIZE 1 SS OVERLOAD 0.8-1.7A-CR324CXDS Nema Overload Relay
Long Description:	Cr324 OL are availbe in Thermal and Electronic Solid-state for size 0-6.
Display Name:	324CXDS

Ordering

Minimum Order Quantity:	1 EA
Customs Tariff Number:	85365040
Product Main Type:	Nema Overload Relay

Dimensions

Product Net Width:	3.6 in
Product Net Depth / Length:	3.77 in
Product Net Height:	3.7 in
Product Net Weight:	1.324 lb

Technical UL/CSA

NEMA Size:	1
------------	---

Material Compliance

WEEE B2C / B2B:	Business To Business
WEEE Category:	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations

UL Certificate:	20150615-E2403
UL Listing Card:	20150615-E2403

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	4 in
Package Level 1 Depth / Length:	4 in
Package Level 1 Height:	4 in
Package Level 1 Gross Weight:	1.4 lb

External Classifications and Standards

eClass:	V11.1 : 27370905
ETIM 6:	EC001037 - Motor starter/Motor starter combination
ETIM 7:	EC001037 - Motor starter/Motor starter combination
ETIM 8:	EC001037 - Motor starter/Motor starter combination
UNSPSC:	39121521

Categories

Products > Low Voltage Products and Systems > Control Products > Contactor Starters > Enclosed Starters



360°