



 PRODUCT-DETAILS

CR324FXMS

SIZE 3&4 SS OVERLOAD 65-135A-CR324FXMS

Nema Overload Relay



360°

General Information

Global Commercial Alias	CR324FXMS
Extended Product Type	SIZE 3&4 SS OVERLOAD 65-135A-CR324FXMS
Product ID	7GSP021549R0006
Catalog Description	SIZE 3&4 SS OVERLOAD 65-135A-CR324FXMS Nema Overload Relay
Long Description	Cr324 OL are availbe in Thermal and Electronic Solid-state for size 0-6.

Ordering

Minimum Order Quantity	1 EA
Customs Tariff Number	85365040
Product Main Type	Nema Overload Relay

Dimensions

Product Net Width	5.06 in
Product Net Depth / Length	6.25 in

Product Net Height	5.26 in
Product Net Weight	3.3 lb

Technical UL/CSA

NEMA Size	4
-----------	---

Material Compliance

WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations

UL Certificate	E103664
----------------	---------

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	5.75 in
Package Level 1 Depth / Length	7.5 in
Package Level 1 Height	6.25 in
Package Level 1 Gross Weight	3.3 lb

Classifications

eClass	V11.1 : 27370905
ETIM 6	EC001037 - Motor starter/Motor starter combination
ETIM 7	EC001037 - Motor starter/Motor starter combination
ETIM 8	EC001037 - Motor starter/Motor starter combination
ETIM 9	EC001037 - Motor starter/motor starter combination
UNSPSC	39121521

Categories

Low Voltage Products and Systems → Control Products → Contactor Starters → Enclosed Starters



360°