

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K3562	9T58R3562G07	1	60	CU	0.50	240x480	12/24	100	40	10225	NONE	Leads Out
9T58K3932	9T58R3932G07	1	60	CU	0.14	480	277	55	40	6100	NONE	Leads Out
9T58K4083	9T58R4083G07	1	50	CU	0.20	115x230	230/460	80	40	8200	NONE	Leads Out
9T58K4084	9T58R4084G07	1	50	CU	0.30	115/230	43	80	40	10225	NONE	Leads Out
9T58K4170	9T58R4170G07	1	60	CU	0.25	208	115	80	40	8200	NONE	Leads Out
9T58K4175	9T58R4175G07	1	60	CU	1.50	208	82	100	40	14225	NONE	Leads Out
9T58K7781	9T58R7781G07	1	50	CU	0.15	575	120	100	40	8175	NONE	Leads Out
9T58K0047G24	9T58R0047G11	1	60	CU	0.25	230x460	115	80	40	8200	(1) QUARTER-INCH	Screw Terminals
9T58K0067G24	9T58R0067G11	1	50	CU	0.25	230/460/575	115/95	100	40	8250	(1) QUARTER-INCH	Screw Terminals
9T58K2802G24	9T58R2802G11	1	60	CU	0.05	240x480	120/240	55	40	6100	(1) QUARTER-INCH	Screw Terminals
9T58K2803G24	9T58R2803G11	1	60	CU	0.08	240x480	120/240	55	40	6125	(1) QUARTER-INCH	Screw Terminals
9T58K2804G24	9T58R2804G11	1	60	CU	0.10	240x480	120/240	55	40	8100	(1) QUARTER-INCH	Screw Terminals
9T58K2805G24	9T58R2805G11	1	60	CU	0.15	240x480	120/240	55	40	8150	(1) QUARTER-INCH	Screw Terminals
9T58K2806G24	9T58R2806G11	1	60	CU	0.20	240x480	120/240	80	40	8175	(1) QUARTER-INCH	Screw Terminals
9T58K2808G24	9T58R2808G11	1	60	CU	0.30	240x480	120/240	100	40	8200	(1) QUARTER-INCH	Screw Terminals
9T58K2810G24	9T58R2810G11	1	60	CU	0.50	240x480	120/240	100	40	10225	(1) QUARTER-INCH	Screw Terminals
9T58K2824G24	9T58R2824G11	1	60	CU	0.10	600	120/240	55	40	8100	(1) QUARTER-INCH	Screw Terminals
9T58K2826G24	9T58R2826G11	1	60	CU	0.20	600	120/240	80	40	8175	(1) QUARTER-INCH	Screw Terminals
9T58K2874G24	9T58R2874G11	1	60	CU	0.08	120x240	12/24	55	40	6125	(1) QUARTER-INCH	Screw Terminals
9T58K2875G24	9T58R2875G11	1	60	CU	0.10	120x240	12/24	55	40	8100	(1) QUARTER-INCH	Screw Terminals
9T58K3164G24	9T58R3164G11	1	60	CU	0.05	240x480	12/24	55	40	6100	(1) QUARTER-INCH	Screw Terminals
9T58K4052G24	9T58R4052G11	1	60	CU	0.15	208/240	12/24	55	40	8150	(1) QUARTER-INCH	Screw Terminals
9T58K4133G24	9T58R4133G11	1	60	CU	0.15	240x480	12/24	55	40	8150	(1) QUARTER-INCH	Screw Terminals
9T58K0042G42	9T58R0042G21	1	60	CU	0.05	230x460	115	55	40	6100	(1) MIDGET	Screw Terminals
9T58K0043G42	9T58R0043G21	1	60	CU	0.08	240x480	120	55	40	6125	(1) MIDGET	Screw Terminals
9T58K0044G42	9T58R0044G21	1	60	CU	0.10	230x460	115	55	40	8100	(1) MIDGET	Screw Terminals
9T58K0045G42	9T58R0045G21	1	60	CU	0.15	230x460	115	55	40	8150	(1) MIDGET	Screw Terminals
9T58K0046G42	9T58R0046G21	1	60	CU	0.20	230x460	115	80	40	8175	(1) MIDGET	Screw Terminals
9T58K0047G42	9T58R0047G21	1	60	CU	0.25	230x460	115	80	40	8200	(1) MIDGET	Screw Terminals
9T58K0050G42	9T58R0050G21	1	60	CU	0.50	230x460	115	80	40	10225	(1) MIDGET	Screw Terminals
9T58K0082G42	9T58R0082G21	1	50	CU	0.05	208/277/380	115/95	55	40	6150	(1) MIDGET	Screw Terminals
9T58K2805G42	9T58R2805G21	1	60	CU	0.15	240x480	120/240	55	40	8150	(1) MIDGET	Screw Terminals
9T58K2807G42	9T58R2807G21	1	60	CU	0.25	240x480	120/240	80	40	8200	(1) MIDGET	Screw Terminals
9T58K2808G42	9T58R2808G21	1	60	CU	0.30	240x480	120/240	115	40	8200	(1) MIDGET	Screw Terminals
9T58K2873G42	9T58R2873G21	1	60	CU	0.05	120x240	12/24	55	40	6100	(1) MIDGET	Screw Terminals
9T58K2874G42	9T58R2874G21	1	60	CU	0.08	120x240	12/24	55	40	6125	(1) MIDGET	Screw Terminals