

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K2875G42	9T58R2875G21	1	60	CU	0.10	120x240	12/24	55	40	8100	(1) MIDGET	Screw Terminals
9T58K2876G42	9T58R2876G21	1	60	CU	0.15	120x240	12/24	55	40	8150	(1) MIDGET	Screw Terminals
9T58K2878G42	9T58R2878G21	1	60	CU	0.25	120x240	12/24	115	40	8200	(1) MIDGET	Screw Terminals
9T58K4145G42	9T58R4145G21	1	50	CU	0.15	230/460/575	115	80	40	8200	(1) MIDGET	Screw Terminals
9T58K4148G42	9T58R4148G21	1	50	CU	0.08	230x460	115	55	40	6150	(1) MIDGET	Screw Terminals
9T58K0043G10	9T58R0043G31	1	60	CU	0.08	240x480	120	55	40	6125	(1) H/K	Screw Terminals
9T58K0047G10	9T58R0047G31	1	60	CU	0.25	230x460	115	80	40	8200	(1) H/K	Screw Terminals
9T58K0050G10	9T58R0050G31	1	60	CU	0.50	230x460	115	80	40	10225	(1) H/K	Screw Terminals
9T58K0052G10	9T58R0052G31	1	60	CU	1.00	230x460	115	80	40	12300	(1) H/K	Screw Terminals
9T58K0054G10	9T58R0054G31	1	60	CU	2.00	240x480	120	100	40	14300	(1) H/K	Screw Terminals
9T58K0070G10	9T58R0070G31	1	50	CU	0.50	230/460/575	115/95	115	40	10225	(1) H/K	Screw Terminals
9T58K0072G10	9T58R0072G31	1	50	CU	1.00	230/460/575	115/95	100	40	14225	(1) H/K	Screw Terminals
9T58K0074G10	9T58R0074G31	1	50	CU	2.00	230/460/575	115/95	100	40	14475	(1) H/K	Screw Terminals
9T58K2804G10	9T58R2804G31	1	60	CU	0.10	240x480	120/240	55	40	8100	(1) H/K	Screw Terminals
9T58K2805G10	9T58R2805G31	1	60	CU	0.15	240x480	120/240	55	40	8150	(1) H/K	Screw Terminals
9T58K2808G10	9T58R2808G31	1	60	CU	0.30	240x480	120/240	100	40	8200	(1) H/K	Screw Terminals
9T58K0044G43	9T58R0044G41	1	60	CU	0.10	230x460	115	55	40	8100	(2) CC	Screw Terminals
9T58K0045G43	9T58R0045G41	1	60	CU	0.15	230x460	115	55	40	8150	(2) CC	Screw Terminals
9T58K0064G43	9T58R0064G41	1	50	CU	0.10	230/460/575	115/95	55	40	8150	(2) CC	Screw Terminals
9T58K0065G43	9T58R0065G41	1	50	CU	0.15	230/460/575	115/95	80	40	8200	(2) CC	Screw Terminals
9T58K0084G43	9T58R0084G41	1	50	CU	0.10	208/277/380	115/95	55	40	8150	(2) CC	Screw Terminals
9T58K0085G43	9T58R0085G41	1	50	CU	0.15	208/277/380	115/95	80	40	8200	(2) CC	Screw Terminals
9T58K3478G43	9T58R3478G41	1	50	CU	0.15	240	24-120	80	40	8175	(2) CC	Screw Terminals
9T58K0042G05	9T58R0042G51	1	60	CU	0.05	230x460	115	55	40	6100	(2) H/K	Screw Terminals
9T58K0044G05	9T58R0044G51	1	60	CU	0.10	230x460	115	55	40	8100	(2) H/K	Screw Terminals
9T58K0045G05	9T58R0045G51	1	60	CU	0.15	230x460	115	55	40	8150	(2) H/K	Screw Terminals
9T58K0048G05	9T58R0048G51	1	60	CU	0.30	230x460	115	80	40	8250	(2) H/K	Screw Terminals
9T58K0064G05	9T58R0064G51	1	50	CU	0.10	230/460/575	115/95	55	40	8150	(2) H/K	Screw Terminals
9T58K2804G05	9T58R2804G51	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) H/K	Screw Terminals
9T58K3019G05	9T58R3019G51	1	60	CU	0.72	120/240/480	82/24	115	40	12225	(2) H/K	Screw Terminals
9T58K1805G05	9T58R1805G57	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) H/K	Leads Out
9T58K1808G05	9T58R1808G57	1	60	CU	0.30	240x480	120/240	100	40	8200	(2) H/K	Leads Out
9T58K0042G48	9T58R0042G61	1	60	CU	0.05	230x460	115	55	40	6100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0043G48	9T58R0043G61	1	60	CU	0.08	240x480	120	55	40	6125	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0044G48	9T58R0044G61	1	60	CU	0.10	230x460	115	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0045G48	9T58R0045G61	1	60	CU	0.15	230x460	115	55	40	8150	(2) CC + (1) QUARTER-INCH	Screw Terminals