

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K2913G48	9T58R2913G61	1	60	CU	0.50	120x240	120/240	80	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K2930G48	9T58R2930G61	1	50	CU	0.50	240x480	120/240	115	40	10225	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K3024G48	9T58R3024G61	1	60	CU	0.25	240x480	12/24	80	40	8200	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K3164G48	9T58R3164G61	1	60	CU	0.05	240x480	12/24	55	40	6100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K4051G48	9T58R4051G61	1	60	CU	0.10	208/240	12/24	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K4132G48	9T58R4132G61	1	60	CU	0.10	240x480	12/24	55	40	8100	(2) CC + (1) QUARTER-INCH	Screw Terminals
9T58K0042G38	9T58R0042G71	1	60	CU	0.05	230x460	115	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K0043G38	9T58R0043G71	1	60	CU	0.08	240x480	120	55	40	6125	(2) CC + (1) MIDGET	Screw Terminals
9T58K0044G38	9T58R0044G71	1	60	CU	0.10	230x460	115	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K0045G38	9T58R0045G71	1	60	CU	0.15	230x460	115	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K0046G38	9T58R0046G71	1	60	CU	0.20	230x460	115	80	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K0047G38	9T58R0047G71	1	60	CU	0.25	230x460	115	80	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K0048G38	9T58R0048G71	1	60	CU	0.30	230x460	115	80	40	8250	(2) CC + (1) MIDGET	Screw Terminals
9T58K0049G38	9T58R0049G71	1	60	CU	0.38	230x460	115	100	40	8250	(2) CC + (1) MIDGET	Screw Terminals
9T58K0050G38	9T58R0050G71	1	60	CU	0.50	230x460	115	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0051G38	9T58R0051G71	1	60	CU	0.75	230x460	115	80	40	12225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0052G38	9T58R0052G71	1	60	CU	1.00	230x460	115	80	40	12300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0055G38	9T58R0055G71	1	60	CU	3.00	230x460	115	115	40	14475	(2) CC + (1) MIDGET	Screw Terminals
9T58K0070G38	9T58R0070G71	1	50	CU	0.50	230/460/575	115/95	115	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0071G38	9T58R0071G71	1	50	CU	0.75	230/460/575	115/95	100	40	12300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0072G38	9T58R0072G71	1	50	CU	1.00	230/460/575	115/95	100	40	14225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0073G38	9T58R0073G71	1	50	CU	1.50	230/460/575	115/95	100	40	14300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0074G38	9T58R0074G71	1	50	CU	2.00	230/460/575	115/95	100	40	14475	(2) CC + (1) MIDGET	Screw Terminals
9T58K0082G38	9T58R0082G71	1	50	CU	0.05	208/277/380	115/95	55	40	6150	(2) CC + (1) MIDGET	Screw Terminals
9T58K0083G38	9T58R0083G71	1	50	CU	0.08	208/277/380	115/95	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K0084G38	9T58R0084G71	1	50	CU	0.10	208/277/380	115/95	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K0085G38	9T58R0085G71	1	50	CU	0.15	208/277/380	115/95	80	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K0086G38	9T58R0086G71	1	50	CU	0.20	208/277/380	115/95	100	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K0087G38	9T58R0087G71	1	50	CU	0.25	208/277/380	115/95	100	40	8250	(2) CC + (1) MIDGET	Screw Terminals
9T58K0088G38	9T58R0088G71	1	50	CU	0.30	208/277/380	115/95	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0089G38	9T58R0089G71	1	50	CU	0.38	208/277/380	115/95	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0090G38	9T58R0090G71	1	50	CU	0.50	208/277/380	115/95	115	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0091G38	9T58R0091G71	1	50	CU	0.75	208/277/380	115/95	80	40	12300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0092G38	9T58R0092G71	1	50	CU	1.00	208/277/380	115/95	100	40	14225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0093G38	9T58R0093G71	1	50	CU	1.50	208/277/380	115/95	100	40	14300	(2) CC + (1) MIDGET	Screw Terminals
9T58K0094G38	9T58R0094G71	1	50	CU	2.00	208/277/380	115/95	100	40	14475	(2) CC + (1) MIDGET	Screw Terminals