

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K1945G38	9T58R1945G71	1	60	CU	0.30	575	120	100	40	8250	(2) CC + (1) MIDGET	Screw Terminals
9T58K2802G38	9T58R2802G71	1	60	CU	0.05	240x480	120/240	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2804G38	9T58R2804G71	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2805G38	9T58R2805G71	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K2806G38	9T58R2806G71	1	60	CU	0.20	240x480	120/240	80	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2807G38	9T58R2807G71	1	60	CU	0.25	240x480	120/240	80	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K2808G38	9T58R2808G71	1	60	CU	0.30	240x480	120/240	100	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K2810G38	9T58R2810G71	1	60	CU	0.50	240x480	120/240	100	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2812G38	9T58R2812G71	1	60	CU	1.00	240x480	120/240	100	40	12300	(2) CC + (1) MIDGET	Screw Terminals
9T58K2813G38	9T58R2813G71	1	60	CU	1.50	240x480	120/240	100	40	14225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2814G38	9T58R2814G71	1	60	CU	2.00	240x480	120/240	115	40	14300	(2) CC + (1) MIDGET	Screw Terminals
9T58K2815G38	9T58R2815G71	1	60	CU	3.00	240x480	120/240	100	40	14475	(2) CC + (1) MIDGET	Screw Terminals
9T58K2824G38	9T58R2824G71	1	60	CU	0.10	600	120/240	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2850G38	9T58R2850G71	1	60	CU	0.05	208/230/460	24-120	55	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2851G38	9T58R2851G71	1	60	CU	0.10	208/230/460	24-120	55	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2852G38	9T58R2852G71	1	60	CU	0.15	208/230/460	24-120	80	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2853G38	9T58R2853G71	1	60	CU	0.25	208/230/460	24-120	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2854G38	9T58R2854G71	1	60	CU	0.30	208/230/460	24-120	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2855G38	9T58R2855G71	1	60	CU	0.35	208/230/460	24-120	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2856G38	9T58R2856G71	1	60	CU	0.50	208/230/460	24-120	80	40	12225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2873G38	9T58R2873G71	1	60	CU	0.05	120x240	12/24	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2874G38	9T58R2874G71	1	60	CU	0.08	120x240	12/24	55	40	6125	(2) CC + (1) MIDGET	Screw Terminals
9T58K2875G38	9T58R2875G71	1	60	CU	0.10	120x240	12/24	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2876G38	9T58R2876G71	1	60	CU	0.15	120x240	12/24	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K2878G38	9T58R2878G71	1	60	CU	0.25	120x240	12/24	100	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K2879G38	9T58R2879G71	1	60	CU	0.30	120x240	12/24	100	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K2907G38	9T58R2907G71	1	60	CU	0.10	120x240	120/240	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K2909G38	9T58R2909G71	1	60	CU	0.20	120x240	120/240	80	40	8175	(2) CC + (1) MIDGET	Screw Terminals
9T58K2911G38	9T58R2911G71	1	60	CU	0.30	120x240	120/240	115	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2913G38	9T58R2913G71	1	60	CU	0.50	120x240	120/240	80	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K2978G38	9T58R2978G71	1	50	CU	0.50	380/400/416	115/230	115	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K3024G38	9T58R3024G71	1	60	CU	0.25	240x480	12/24	80	40	8200	(2) CC + (1) MIDGET	Screw Terminals
9T58K3118G38	9T58R3118G71	1	60	CU	0.05	208	12/24	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K3119G38	9T58R3119G71	1	60	CU	0.08	208	12/24	55	40	6125	(2) CC + (1) MIDGET	Screw Terminals
9T58K3120G38	9T58R3120G71	1	60	CU	0.10	208	12/24	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K3125G38	9T58R3125G71	1	60	CU	0.30	240x480	24	115	40	8200	(2) CC + (1) MIDGET	Screw Terminals