

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K3164G38	9T58R3164G71	1	60	CU	0.05	240x480	12/24	55	40	6100	(2) CC + (1) MIDGET	Screw Terminals
9T58K4132G38	9T58R4132G71	1	60	CU	0.10	240x480	12/24	55	40	8100	(2) CC + (1) MIDGET	Screw Terminals
9T58K4133G38	9T58R4133G71	1	60	CU	0.15	240x480	12/24	55	40	8150	(2) CC + (1) MIDGET	Screw Terminals
9T58K4174G38	9T58R4174G71	1	50	CU	1.50	380/415/480	120	100	40	14300	(2) CC + (1) MIDGET	Screw Terminals
9T58K4194G38	9T58R4194G71	1	60	CU	0.25	208/240/480	24-120	100	40	10225	(2) CC + (1) MIDGET	Screw Terminals
9T58K0504G38	9T58R0504G77	1	60	CU	0.15	480	120	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0517G38	9T58R0517G77	1	60	CU	0.30	208	120	80	40	8250	(2) CC + (1) MIDGET	Leads Out
9T58K0534G38	9T58R0534G77	1	60	CU	0.15	600	120	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0537G38	9T58R0537G77	1	60	CU	0.30	600	120	80	40	8250	(2) CC + (1) MIDGET	Leads Out
9T58K0574G38	9T58R0574G77	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0577G38	9T58R0577G77	1	60	CU	0.30	240x480	120/240	80	40	8250	(2) CC + (1) MIDGET	Leads Out
9T58K0702G38	9T58R0702G77	1	60	CU	0.15	480	24	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0944G38	9T58R0944G77	1	60	CU	0.15	208	120	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0953G38	9T58R0953G77	1	50	CU	0.10	380/400/416	110/220	55	40	8150	(2) CC + (1) MIDGET	Leads Out
9T58K0957G38	9T58R0957G77	1	50	CU	0.25	380/400/415	110/220	80	40	8250	(2) CC + (1) MIDGET	Leads Out
9T58K1696G38	9T58R1696G77	1	50	CU	0.15	380/400/415	110/220	80	40	8175	(2) CC + (1) MIDGET	Leads Out
9T58K1803G38	9T58R1803G77	1	60	CU	0.08	240x480	120/240	55	40	6125	(2) CC + (1) MIDGET	Leads Out
9T58K1804G38	9T58R1804G77	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) CC + (1) MIDGET	Leads Out
9T58K1806G38	9T58R1806G77	1	60	CU	0.20	240x480	120/240	80	40	8175	(2) CC + (1) MIDGET	Leads Out
9T58K0042G18	9T58R0042G81	1	60	CU	0.05	230x460	115	55	40	6100	(2) CC + (1) H/K	Screw Terminals
9T58K0043G18	9T58R0043G81	1	60	CU	0.08	240x480	120	55	40	6125	(2) CC + (1) H/K	Screw Terminals
9T58K0044G18	9T58R0044G81	1	60	CU	0.10	230x460	115	55	40	8100	(2) CC + (1) H/K	Screw Terminals
9T58K0045G18	9T58R0045G81	1	60	CU	0.15	230x460	115	55	40	8150	(2) CC + (1) H/K	Screw Terminals
9T58K0046G18	9T58R0046G81	1	60	CU	0.20	230x460	115	80	40	8175	(2) CC + (1) H/K	Screw Terminals
9T58K0047G18	9T58R0047G81	1	60	CU	0.25	230x460	115	80	40	8200	(2) CC + (1) H/K	Screw Terminals
9T58K0048G18	9T58R0048G81	1	60	CU	0.30	230x460	115	80	40	8250	(2) CC + (1) H/K	Screw Terminals
9T58K0050G18	9T58R0050G81	1	60	CU	0.50	230x460	115	80	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K0062G18	9T58R0062G81	1	50	CU	0.05	230/460/575	115/95	55	40	6150	(2) CC + (1) H/K	Screw Terminals
9T58K0067G18	9T58R0067G81	1	50	CU	0.25	230/460/575	115/95	100	40	8250	(2) CC + (1) H/K	Screw Terminals
9T58K0070G18	9T58R0070G81	1	50	CU	0.50	230/460/575	115/95	115	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K0082G18	9T58R0082G81	1	50	CU	0.05	208/277/380	115/95	55	40	6150	(2) CC + (1) H/K	Screw Terminals
9T58K0084G18	9T58R0084G81	1	50	CU	0.10	208/277/380	115/95	55	40	8150	(2) CC + (1) H/K	Screw Terminals
9T58K0087G18	9T58R0087G81	1	50	CU	0.25	208/277/380	115/95	100	40	8250	(2) CC + (1) H/K	Screw Terminals
9T58K0090G18	9T58R0090G81	1	50	CU	0.50	208/277/380	115/95	115	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K0091G18	9T58R0091G81	1	50	CU	0.75	208/277/380	115/95	80	40	12300	(2) CC + (1) H/K	Screw Terminals
9T58K0092G18	9T58R0092G81	1	50	CU	1.00	208/277/380	115/95	100	40	14225	(2) CC + (1) H/K	Screw Terminals