

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K0726G18	9T58R0726G81	1	50	CU	0.10	480	120	80	40	8200	(2) CC + (1) H/K	Screw Terminals
9T58K0730G18	9T58R0730G81	1	50	CU	0.30	480	120	100	40	8250	(2) CC + (1) H/K	Screw Terminals
9T58K1001G18	9T58R1001G81	1	60	CU	0.20	525	126/145	100	40	8175	(2) CC + (1) H/K	Screw Terminals
9T58K2802G18	9T58R2802G81	1	60	CU	0.05	240x480	120/240	55	40	6100	(2) CC + (1) H/K	Screw Terminals
9T58K2803G18	9T58R2803G81	1	60	CU	0.08	240x480	120/240	55	40	6125	(2) CC + (1) H/K	Screw Terminals
9T58K2804G18	9T58R2804G81	1	60	CU	0.10	240x480	120/240	55	40	8100	(2) CC + (1) H/K	Screw Terminals
9T58K2805G18	9T58R2805G81	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) H/K	Screw Terminals
9T58K2806G18	9T58R2806G81	1	60	CU	0.20	240x480	120/240	80	40	8175	(2) CC + (1) H/K	Screw Terminals
9T58K2807G18	9T58R2807G81	1	60	CU	0.25	240x480	120/240	80	40	8200	(2) CC + (1) H/K	Screw Terminals
9T58K2808G18	9T58R2808G81	1	60	CU	0.30	240x480	120/240	115	40	8200	(2) CC + (1) H/K	Screw Terminals
9T58K2810G18	9T58R2810G81	1	60	CU	0.50	240x480	120/240	100	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K2812G18	9T58R2812G81	1	60	CU	1.00	240x480	120/240	100	40	12300	(2) CC + (1) H/K	Screw Terminals
9T58K2813G18	9T58R2813G81	1	60	CU	1.50	240x480	120/240	100	40	14225	(2) CC + (1) H/K	Screw Terminals
9T58K2824G18	9T58R2824G81	1	60	CU	0.10	600	120/240	55	40	8100	(2) CC + (1) H/K	Screw Terminals
9T58K2830G18	9T58R2830G81	1	60	CU	0.50	600	120/240	80	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K2873G18	9T58R2873G81	1	60	CU	0.05	120x240	12/24	55	40	6100	(2) CC + (1) H/K	Screw Terminals
9T58K2875G18	9T58R2875G81	1	60	CU	0.10	120x240	12/24	55	40	8100	(2) CC + (1) H/K	Screw Terminals
9T58K2930G18	9T58R2930G81	1	50	CU	0.50	240x480	120/240	115	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K3467G18	9T58R3467G81	1	60	CU	0.50	240x480	115	100	40	10225	(2) CC + (1) H/K	Screw Terminals
9T58K4174G18	9T58R4174G81	1	50	CU	1.50	380/415/480	120	100	40	14300	(2) CC + (1) H/K	Screw Terminals
9T58K0501G18	9T58R0501G87	1	60	CU	0.06	480	120	55	40	6100	(2) CC + (1) H/K	Leads Out
9T58K0503G18	9T58R0503G87	1	60	CU	0.10	480	120	55	40	8100	(2) CC + (1) H/K	Leads Out
9T58K0504G18	9T58R0504G87	1	60	CU	0.15	480	120	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0507G18	9T58R0507G87	1	60	CU	0.30	480	120	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0511G18	9T58R0511G87	1	60	CU	0.06	208	120	55	40	6100	(2) CC + (1) H/K	Leads Out
9T58K0517G18	9T58R0517G87	1	60	CU	0.30	208	120	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0534G18	9T58R0534G87	1	60	CU	0.15	600	120	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0537G18	9T58R0537G87	1	60	CU	0.30	600	120	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0574G18	9T58R0574G87	1	60	CU	0.15	240x480	120/240	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0577G18	9T58R0577G87	1	60	CU	0.30	240x480	120/240	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0702G18	9T58R0702G87	1	60	CU	0.15	480	24	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0705G18	9T58R0705G87	1	60	CU	0.30	480	24	80	40	8250	(2) CC + (1) H/K	Leads Out
9T58K0944G18	9T58R0944G87	1	60	CU	0.15	208	120	55	40	8150	(2) CC + (1) H/K	Leads Out
9T58K0954G18	9T58R0954G87	1	50	CU	0.15	380/400/415	110/220	80	40	8175	(2) CC + (1) H/K	Leads Out
9T58K0956G18	9T58R0956G87	1	50	CU	0.25	380/400/416	110/220	80	40	8250	(2) CC + (1) H/K	Leads Out