

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K2934	9T58R2934	1	50	CU	2.00	240x480	120/240	100	40	14475	NONE	Screw Terminals
9T58K2935	9T58R2935	1	50	CU	3.00	240x480	120/240	115	40	14475	NONE	Screw Terminals
9T58K2959	9T58R2959	1	50	CU	0.25	600	120/240	100	40	8200	NONE	Screw Terminals
9T58K2975	9T58R2975	1	50	CU	0.25	380/400/416	115/230	115	40	8200	NONE	Screw Terminals
9T58K2978	9T58R2978	1	50	CU	0.50	380/400/416	115/230	115	40	10225	NONE	Screw Terminals
9T58K2979	9T58R2979	1	50	CU	0.75	380/400/416	115/230	100	40	12300	NONE	Screw Terminals
9T58K2980	9T58R2980	1	50	CU	1.00	380/400/416	115/230	100	40	14225	NONE	Screw Terminals
9T58K2981	9T58R2981	1	50	CU	1.50	380/400/416	115/230	100	40	14300	NONE	Screw Terminals
9T58K2982	9T58R2982	1	50	CU	2.00	380/400/416	115/230	100	40	14475	NONE	Screw Terminals
9T58K2983	9T58R2983	1	50	CU	3.00	380/400/416	115/230	115	40	14475	NONE	Screw Terminals
9T58K2984	9T58R2984	1	50	CU	2.00	200/208/240/380/416	115/230	100	40	14475	NONE	Screw Terminals
9T58K2985	9T58R2985	1	50	CU	1.00	380/416/460	115/230	100	40	14225	NONE	Screw Terminals
9T58K3005	9T58R3005	1	60	CU	0.35	208/230	115	100	40	8250	NONE	Screw Terminals
9T58K3010	9T58R3010	1	50	CU	0.25	208/230/460	115/95	100	40	8250	NONE	Screw Terminals
9T58K3015	9T58R3015	1	60	CU	0.28	240x480	80/115/230	100	40	10225	NONE	Screw Terminals
9T58K3023	9T58R3023	1	50	CU	1.50	380/400/415	82	100	40	14300	NONE	Screw Terminals
9T58K3024	9T58R3024	1	60	CU	0.25	240x480	12/24	80	40	8200	NONE	Screw Terminals
9T58K3027	9T58R3027	1	60	CU	0.10	240x480	24	55	40	8100	NONE	Screw Terminals
9T58K3028	9T58R3028	1	60	CU	0.15	240x480	24	55	40	8150	NONE	Screw Terminals
9T58K3092	9T58R3092	1	50	CU	0.25	208/240/480	115	100	40	8250	NONE	Screw Terminals
9T58K3101	9T58R3101	1	60	CU	0.08	208/230/460	115	55	40	6150	NONE	Screw Terminals
9T58K3113	9T58R3113	1	50	CU	0.50	380/480/575	120/240	115	40	10225	NONE	Screw Terminals
9T58K3120	9T58R3120	1	60	CU	0.10	208	12/24	55	40	8100	NONE	Screw Terminals
9T58K3127	9T58R3127	1	50	CU	0.15	400	105	55	40	8175	NONE	Screw Terminals
9T58K3128	9T58R3128	1	50	CU	0.50	400	105	55	40	12225	NONE	Screw Terminals
9T58K3135	9T58R3135	1	60	CU	0.25	240x480	115	55	40	8250	NONE	Screw Terminals
9T58K3144	9T58R3144	1	60	CU	1.00	208	120/240	100	40	12300	NONE	Screw Terminals
9T58K3145	9T58R3145	1	50	CU	1.00	200/220	120/240	100	40	14225	NONE	Screw Terminals
9T58K3154	9T58R3154	1	50	CU	0.05	380/460/575	24	55	40	6150	NONE	Screw Terminals
9T58K3158	9T58R3158	1	60	CU	0.50	208/240/480	12/24	100	40	10225	NONE	Screw Terminals
9T58K3159	9T58R3159	1	60	CU	0.15	208/240	27	100	40	8175	NONE	Screw Terminals
9T58K3160	9T58R3160	1	60	CU	0.25	230x460	120/240	100	40	8200	NONE	Screw Terminals
9T58K3161	9T58R3161	1	60	CU	0.05	208/230/460	120	55	40	6100	NONE	Screw Terminals
9T58K3164	9T58R3164	1	60	CU	0.05	240x480	12/24	55	40	6100	NONE	Screw Terminals
9T58K3167	9T58R3167	1	60	CU	0.30	480	24	100	40	8200	NONE	Screw Terminals
9T58K3172	9T58R3172	1	60	CU	2.00	240x480	115	55	40	14475	NONE	Screw Terminals