

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K3931	9T58R3931	1	60	CU	0.90	332	266	115	40	8175	NONE	Screw Terminals
9T58K4033	9T58R4033	1	50	CU	0.50	380/460	120-24	115	40	10225	NONE	Screw Terminals
9T58K4050	9T58R4050	1	60	CU	0.05	208/240	12/24	55	40	6100	NONE	Screw Terminals
9T58K4051	9T58R4051	1	60	CU	0.10	208/240	12/24	55	40	8100	NONE	Screw Terminals
9T58K4052	9T58R4052	1	60	CU	0.15	208/240	12/24	55	40	8150	NONE	Screw Terminals
9T58K4053	9T58R4053	1	60	CU	0.25	208/240	12/24	100	40	8200	NONE	Screw Terminals
9T58K4132	9T58R4132	1	60	CU	0.10	240x480	12/24	55	40	8100	NONE	Screw Terminals
9T58K4133	9T58R4133	1	60	CU	0.15	240x480	12/24	55	40	8150	NONE	Screw Terminals
9T58K4136	9T58R4136	1	60	CU	0.05	220/380/460	120	55	40	6125	NONE	Screw Terminals
9T58K4137	9T58R4137	1	60	CU	0.08	220/380/460	24	55	40	8100	NONE	Screw Terminals
9T58K4141	9T58R4141	1	60	CU	1.00	150/208/220/240	70	100	40	14225	NONE	Screw Terminals
9T58K4152	9T58R4152	1	60	CU	0.20	208/240/480	120	80	40	8200	NONE	Screw Terminals
9T58K4159	9T58R4159	1	60	CU	0.50	208/230/460	115	115	40	10225	NONE	Screw Terminals
9T58K4161	9T58R4161	1	50	CU	0.50	208/230/460	115	115	40	12225	NONE	Screw Terminals
9T58K4166	9T58R4166	1	50	CU	0.05	120x240	12/24	55	40	6100	NONE	Screw Terminals
9T58K4176	9T58R4176	1	60	CU	0.50	480	277	100	40	10225	NONE	Screw Terminals
9T58K4178	9T58R4178	1	50	CU	0.25	380/415/575	24	100	40	10225	NONE	Screw Terminals
9T58K4179	9T58R4179	1	60	CU	0.25	208/240/480	24	100	40	8250	NONE	Screw Terminals
9T58K4180	9T58R4180	1	60	CU	2.00	380/460	115	100	40	14300	NONE	Screw Terminals
9T58K4183	9T58R4183	1	60	CU	0.20	208/240/480	24	100	40	8200	NONE	Screw Terminals
9T58K4184	9T58R4184	1	50	CU	0.15	230x460	120-24	100	40	10225	NONE	Screw Terminals
9T58K4186	9T58R4186	1	60	CU	0.30	208/230/380/460/575	115	100	40	10225	NONE	Screw Terminals
9T58K4190	9T58R4190	1	60	CU	0.05	208/240/480	24-120	55	40	6150	NONE	Screw Terminals
9T58K4191	9T58R4191	1	60	CU	0.10	208/240/480	24-120	55	40	8150	NONE	Screw Terminals
9T58K4193	9T58R4193	1	50	CU	0.25	208/230/460	24-115	115	40	12225	NONE	Screw Terminals
9T58K4194	9T58R4194	1	60	CU	0.25	208/240/480	24-120	100	40	10225	NONE	Screw Terminals
9T58K4205	9T58R4205	1	50	CU	1.57	210/230/240	24-110/120	115	40	14300	NONE	Screw Terminals
9T58K4206	9T58R4206	1	50	CU	0.57	210/230/240	24-110/120	115	40	12225	NONE	Screw Terminals
9T58K4207	9T58R4207	1	60	CU	0.58	200/230/460/575	24-120	100	40	12225	NONE	Screw Terminals
9T58K4208	9T58R4208	1	50	CU	0.58	380/415	24-120	100	40	12225	NONE	Screw Terminals
9T58K4210	9T58R4210	1	50	CU	0.86	120/240/480	22-80	100	40	14225	NONE	Screw Terminals
9T58K4277	9T58R4277	1	50	CU	0.75	200/220/230/380/400/415	117	115	40	12300	NONE	Screw Terminals
9T58K4290	9T58R4290	1	60	CU	0.50	208	120/240	100	40	10225	NONE	Screw Terminals
9T58K4299	9T58R4299	1	50	CU	0.20	240x480	120	115	40	8175	NONE	Screw Terminals
9T58K4350	9T58R4350	1	50	CU	0.08	120/240	12/24	55	40	8100	NONE	Screw Terminals
9T58K4355	9T58R4355	1	60	CU	0.50	220x440	110/220	100	40	12225	NONE	Screw Terminals