

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K4356	9T58R4356	1	60	CU	0.75	220x440	110/220	100	40	12300	NONE	Screw Terminals
9T58K4357	9T58R4357	1	60	CU	1.00	220x440	110/220	100	40	14225	NONE	Screw Terminals
9T58K4358	9T58R4358	1	60	CU	1.50	220x440	110/220	80	40	14300	NONE	Screw Terminals
9T58K4359	9T58R4359	1	60	CU	2.00	220x440	110/220	100	40	14475	NONE	Screw Terminals
9T58K4360	9T58R4360	1	50	CU	0.10	380/415	24	55	40	8150	NONE	Screw Terminals
9T58K4365	9T58R4365	1	60	CU	0.50	220x440	110/220	100	40	12225	NONE	Screw Terminals
9T58K4366	9T58R4366	1	60	CU	0.75	220x440	110/220	100	40	12300	NONE	Screw Terminals
9T58K4367	9T58R4367	1	60	CU	1.00	220x440	110/220	100	40	14225	NONE	Screw Terminals
9T58K4368	9T58R4368	1	60	CU	1.50	220x440	110/220	80	40	14300	NONE	Screw Terminals
9T58K4369	9T58R4369	1	60	CU	2.00	220x440	110/220	115	40	14475	NONE	Screw Terminals
9T58K4405	9T58R4405	1	60	CU	0.69	200/230/240/460/480	38.5	115	40	12225	NONE	Screw Terminals
9T58K4500	9T58R4500	1	60	CU	0.05	208	120	55	40	6100	NONE	Screw Terminals
9T58K4501	9T58R4501	1	60	CU	0.05	600	120	55	40	6100	NONE	Screw Terminals
9T58K4502	9T58R4502	1	60	CU	0.05	277	120	55	40	6100	NONE	Screw Terminals
9T58K4503	9T58R4503	1	60	CU	0.05	240x480	24	55	40	6100	NONE	Screw Terminals
9T58K4504	9T58R4504	1	60	CU	0.05	120	24	55	40	6100	NONE	Screw Terminals
9T58K4505	9T58R4505	1	60	CU	0.05	208	24	55	40	6100	NONE	Screw Terminals
9T58K4506	9T58R4506	1	60	CU	0.10	208	120	55	40	8150	NONE	Screw Terminals
9T58K4510	9T58R4510	1	60	CU	0.25	600	120	80	40	8200	NONE	Screw Terminals
9T58K4511	9T58R4511	1	60	CU	0.25	208	120	80	40	8200	NONE	Screw Terminals
9T58K4512	9T58R4512	1	60	CU	0.30	600	120	100	40	8250	NONE	Screw Terminals
9T58K4513	9T58R4513	1	60	CU	0.30	208	120	100	40	8250	NONE	Screw Terminals
9T58K4515	9T58R4515	1	60	CU	0.25	208/240/480	120	100	40	8250	NONE	Screw Terminals
9T58K4516	9T58R4516	1	60	CU	0.50	480	24	100	40	10225	NONE	Screw Terminals
9T58K5083	9T58R5083	1	50	CU	0.20	115x230	230/460	80	40	8200	NONE	Screw Terminals
9T58K6143	9T58R6143	1	50	CU	1.50	230/460/575	115	115	40	14300	NONE	Screw Terminals
9T58K7772	9T58R7772	1	60	CU	0.44	208/230/240/460/480	115	80	40	10225	NONE	Screw Terminals
9T58K7773	9T58R7773	1	60	CU	0.35	208/230/240/460/480	24/12-48/24	100	40	10225	NONE	Screw Terminals
9T58K7778	9T58R7778	1	60	CU	1.19	200/230/240/460/480	38.5-115	80	40	12300	NONE	Screw Terminals
9T58K7779	9T58R7779	1	50	CU	0.50	120x240	120/240	80	40	12225	NONE	Screw Terminals
9T58K7780	9T58R7780	1	60	CU	0.05	277	24	55	40	6100	NONE	Screw Terminals
9T58K7782	9T58R7782	1	50	CU	0.20	440/550	200	100	40	8200	NONE	Screw Terminals
9T58K9998	9T58R9998	1	60	CU	0.13	525	128/147	100	40	8175	NONE	Screw Terminals
9T58K0094	9T58R0094G07	1	50	CU	2.00	208/277/380	115/95	100	40	14475	NONE	Leads Out
9T58K0501	9T58R0501G07	1	60	CU	0.06	480	120	55	40	6100	NONE	Leads Out
9T58K0503	9T58R0503G07	1	60	CU	0.10	480	120	55	40	8100	NONE	Leads Out