



Representative Image

## Ref. No. 682228 | Cat. No. EP103ULH2B63

Description: MCB Miniature circuit breaker ElfaPlus EP100 ULH 3P 63A B GE

EAN 5413656822288

Home > Modular DIN-rail devices > Circuit Protection > MCB DIN-rail

- **Safe and reliable**
  - Clear print
  - High degree of insulation IP20
  - Padlocking toggle
  - Sealed terminals
    - **User friendly**
    - **Multifunctional**
- Motor operator : same device left and right assembly
- Common device for all products
  - Shunt trip and under voltage relay
- Auxiliaries
  - **Easy to install**
- >Different connection techniques
- High torque performance 4.5 Nm
- High capacity terminals 35mm<sup>2</sup>

### Descriptors

Category	MCB DIN-rail
Family	Circuit protection

### Specifications

In (A)	63
Number of poles	3P
Number of modules	3
Curve Type	B (3-5 In)
Group	ElfaPlus
Range	Commercial - Industrial
Switch	EP100 ULH : 10kA - UL Listed 489
Connections- Top	Screw
Connections- Bottom	Screw
Standards	10kA domestic BS EN 60898, 10kA UL498, 15-40kA industrial BS EN 60947-2
AC/DC	AC
Logo	GE
Rated voltage	120 V / 240 V
Short-circuit capacity (kA)	10
Selectivity class	3
Terminal capacity max (mm <sup>2</sup> )	25-35 mm <sup>2</sup>
Electrical service life	20000/10000
Minimum operating voltage U <sub>bmin</sub> (V)	12 V
Operating temperature	-25°C / 55°C
Terminal capacity min (mm <sup>2</sup> )	0.75 / 1 mm <sup>2</sup>
Tropicalisation	95%RH at 55°C

### Classifications

## Classifications

Approvals	CCC, CE, CEBEC, EAC, UL
ETIM 5.0	EC000042
ETIM 6.0	EC000042

## Dimensions

Weight	0.390 kg
--------	----------

## Package information

Standard packing	4
------------------	---