

Clip-on Plastic Staples

Secures Romex®, UF and other type-NM cable.

- Fast and easy to install – both zinc-plated nails drive together.
- Hardened nails can penetrate cement block, mortar or plaster surfaces.
- Nail heads are recessed for minimum exposure.
- Smooth saddles prevent damage to cable insulation.
- UV-protected polyethylene saddle resists rot, rust and deterioration.



| Size | Part # | Pkg Qty | Type | Application |
|------|-----------|---------|---------|------------------|
| 1/2" | PSM-1550T | 25/clam | Masonry | 14/2, 12/2, 10/2 |
| | PS-50M | 50/bag | | |
| | PS-225JM | 225/jar | | |

| Size | Part # | Pkg Qty | Type | Application |
|------|----------|---------|---------|------------------|
| 3/4" | PS-75M | 50/bag | Masonry | 14/3, 12/3, 10/3 |
| | PS-175JM | 175/jar | | |



Service Entrance Cable Straps

Plastic insulated straps quickly and easily secure service entrance cable.

- Electro-zinc plated nails provide strength and durability.
- Polyethylene straps stabilized against UV rays and extreme cold; withstand deterioration and breakage.



SER

| Part # | Pkg Qty | Application | Part # | Pkg Qty | Application |
|---------|---------|-------------|---------|---------|-------------|
| GSE-105 | 5/card | | GSE-304 | 4/card | |
| GSE-115 | 10/box | #6 SEU | GSE-314 | 10/box | #2 SER |
| GSE-170 | 70/box | | GSE-330 | 30/box | |
| GSE-205 | 5/card | | GSE-402 | 2/card | #4/0 SEU |
| GSE-215 | 10/box | #2 SEU | GSE-505 | 5/card | |
| GSE-250 | 50/box | | GSE-515 | 10/box | #6 SER |



SEU

Conduit Plastic Straps

Enables secure fastening of plastic electrical conduit, schedule 40 PVC, copper tubing, etc.

- Heavy-duty polyethylene resists deterioration from UV rays and breakage from extreme cold.



| Size Dia. | Part # | Pkg Qty | Application |
|-----------|---------|---------|--------------|
| .840" | GCC-120 | 6/card | 1/2" conduit |
| 1.05" | GCC-220 | 20/bag | 3/4" conduit |
| 1.315" | GCC-310 | 10/bag | 1" conduit |

| Size Dia. | Part # | Pkg Qty | Application |
|-----------|---------|---------|----------------|
| 1.66" | GCC-410 | 10/bag | 1 1/4" conduit |
| 1.9" | GCC-510 | 10/bag | 1 1/2" conduit |
| 2.375" | GCC-610 | 10/bag | 2" conduit |

Coaxial Cable Staples - Low Voltage

Secures RG-59 and RG-6 coaxial cables.

- UV-resistant polyethylene saddle.
- For indoor and outdoor applications.
- Zinc-plated nails resist rust and corrosion.



PCC-1525

PSB-1650

PSG-15



| Size | Part # | Pkg Qty | Color |
|------|-----------|----------|-------|
| 1/4" | PSB-1650T | 25/card | Black |
| | PSW-1650T | 25/card | White |
| | PSB-165 | 50/card | Black |
| | PSW-165 | 50/card | White |
| | PSB-100 | 100/box | Black |
| | PSW-100 | 100/card | White |
| | PSW-200JN | 200/jar | White |

| Size | Part # | Pkg Qty | Color |
|--------|----------|---------|-------|
| 1/4" | PCC-1525 | 25/clam | Black |
| | PSG-15 | 15/card | Gray |
| | PSG-50 | 50/box | Gray |
| 7/16"* | PSG-100 | 100/bag | Gray |
| | PR-50 | 50/bag | White |



*For RG-8, triaxial and up to 25 pairs UTP cable