

Rotary Switches



Single or three position switches in various fan and lighting applications.

- #18 AWG, 6" stripped wire leads.
- Brass terminals.

						
Part Number	GSW-61	GSW-63B	GSW-69	GSW-69BP	GSW-62	GSW-68
Poles	SPST				DP3T	SPTT
Pkg Qty	1/card	1/card	1/card	10/box	1/card	1/card
Toggle Position	ON-OFF	ON-OFF	ON-OFF	ON-OFF	OFF-ON(P)-ON(N) -ON(N+P)	OFF-ON(P)-ON(N) -ON(N+P)
Plating / Color	Brass	Black Button	Black Plastic	Black Plastic	Brass	Brass
Rating	6 A/125 V AC, 3 A/250 V AC	1.5 A/250 V AC	6 A/125 V AC, 3 A/250 V AC	6 A/125 V AC, 3 A/250 V AC	6 A/125 V AC, 3 A/250 V AC	6 A/125 V AC, 3 A/250 V AC
Mounting Hole	.406"	.513"	.513"	.513"	.406"	.513"

Door Switch



Push button switch with metal box, cover plate and mounting hardware to operate lights when door is opened.

- Mounts in door jam.
- Fits in 1.25" X 2.75" X 2.0" deep approximate mounting hole.
- **Specifications:** 16 A/125 V AC, 10 A/250 V AC, 10 A/277 V AC, ½ HP 125 - 277 V AC; 75°C max. temp rating

		
Part Number	GSW-SK	GSW-26
Poles	SPST	
Pkg Qty	1/card	1/card
Toggle Position	Normally ON -Mom Contact	Normally ON -Mom Contact
Description	Door Switch	Replacement for GSW-SK