

## General Purpose Terminals


Quick and reliable crimp-type wire connections.


- Color-coded by wire gauge size.
- Available in a variety of packaging options and stud sizes.
- Includes Spade and Ring Terminals, Disconnects, and Bullet, Butt & Tap Splices (p.17-19)


## Spade Terminals - Vinyl-Insulated Barrel

- Rated at 600 Volt Max.
- Temperature rating: 167 °F (75 °C).




| 22-18 Gauge   | Part # | Pkg Qty | Stud Size |
|---|--------|---------|-----------|
|  | 20-111 | 20/clam | 4 to 6    |
|   | 20-112 | 20/clam | 8 to 10   |
|   | 75-111 | 75/clam | 4 to 6    |

| 16-14 Gauge  | Part # | Pkg Qty  | Stud Size |
|--|--------|----------|-----------|
|  | 10-113 | 100/clam | 4 to 6    |
|  | 10-114 | 100/clam | 8 to 10   |
|  | 15-114 | 15/clam  | 8 to 10   |
|  | 20-113 | 20/clam  | 4 to 6    |
|  | 20-114 | 20/clam  | 8 to 10   |
|  | 75-113 | 75/clam  | 4 to 6    |

| 12-10 Gauge   | Part # | Pkg Qty | Stud Size |
|---|--------|---------|-----------|
|  | 10-116 | 50/clam | 8 to 10   |
|   | 15-116 | 15/clam | 8 to 10   |
|   | 75-116 | 5/clam  | 8 to 10   |

SEE PG  
**122**





FOR MORE INFO ON  
**Crimp Tools**


## Ring Terminals - Vinyl-Insulated Barrel


- Rated at 600 Volt Max.
- Temperature rating: 167 °F (75 °C).




| 22-18 Gauge  | Part # | Pkg Qty | Stud Size |
|--|--------|---------|-----------|
|  | 20-101 | 22/clam | 4 to 6    |
|  | 20-102 | 22/clam | 8 to 10   |
|  | 21-101 | 10/clam | 4 to 6    |
|  | 21-102 | 10/clam | 8 to 10   |

| 16-14 Gauge  | Part #  | Pkg Qty  | Stud Size     |
|--|---------|----------|---------------|
|  | 10-104  | 100/clam | 8 to 10       |
|  | 10-105  | 100/clam | 12 to 1/4"    |
|  | 15-104  | 15/clam  | 8 to 10       |
|  | 15-105  | 15/clam  | 12 to 1/4"    |
|  | 20-103  | 22/clam  | 4 to 6        |
|  | 20-104  | 22/clam  | 8 to 10       |
|  | 20-105  | 17/clam  | 12 to 1/4"    |
|  | 21-1055 | 7/clam   | 5/16" to 3/8" |
|  | 75-104  | 75/clam  | 8 to 10       |

| 12-10 Gauge  | Part # | Pkg Qty | Stud Size     |
|--|--------|---------|---------------|
|  | 10-106 | 50/clam | 8 to 10       |
|  | 10-107 | 50/clam | 12 to 1/4"    |
|  | 10-108 | 50/clam | 1/4" to 3/8"  |
|  | 15-106 | 15/clam | 8 to 10       |
|  | 15-107 | 15/clam | 12 to 1/4"    |
|  | 15-108 | 15/clam | 5/16" to 3/8" |
|  | 20-106 | 14/clam | 8 to 10       |
|  | 20-107 | 14/clam | 12 to 1/4"    |
|  | 20-108 | 13/clam | 1/4" to 3/8"  |
|  | 21-106 | 8/clam  | 8 to 10       |
|  | 21-109 | 7/clam  | 7/16" to 1/2" |
|  | 75-106 | 50/clam | 8 to 10       |

| 6 Gauge  | Part # | Pkg Qty | Stud Size |
|--|--------|---------|-----------|
|  | 14-095 | 4/card  | 1/4"      |
|  | 14-097 | 4/card  | 1/2"      |
|  | 15-096 | 4/card  | 3/8"      |

| 4 Gauge  | Part # | Pkg Qty | Stud Size |
|--|--------|---------|-----------|
|  | 14-099 | 4/card  | 1/2"      |
|  | 15-098 | 4/card  | 3/8"      |