

Butt Splices



- Rated at 600 Volt Max.
- Temperature rating: 167 °F (75 °C).

22-18 Gauge	Part #	Pkg Qty
-------------	--------	---------



10-121	100/clam
15-121	15/clam
20-121	22/clam
21-121	10/clam
75-121	75/clam

16-14 Gauge	Part #	Pkg Qty
-------------	--------	---------



10-123	100/clam
15-123	15/clam
20-123	21/clam
21-123	10/clam
75-123	75/clam

12-10 Gauge	Part #	Pkg Qty
-------------	--------	---------



10-126	50/clam
15-126	15/clam
20-126	15/clam
21-126	8/clam
75-126	50/clam

Terminal Blocks



- Rated at 30 Amp/600 Volt max.
- Temperature rating: -40 °F (-40 °C) to 260 °F (130 °C).
- Wire range 22-10 AWG.
- Accepts #8 stud size.

Part #	No. of Poles	Pkg Qty
GTB-406	6	1/clam
GTB-408	8	1/clam
GTB-410	10	1/clam

Tap Splices

- Secure connections without stripping wire.
- Rated at 600 Volt Max.
- Temperature rating: 221 °F (105 °C).

22-18 Gauge	Part #	Pkg Qty
-------------	--------	---------



15-2218	5/clam
20-2218	5/clam ¹²
21-2218	5/clam ¹³

16-14 Gauge	Part #	Pkg Qty
-------------	--------	---------



10-100	25/clam
20-100	5/clam ¹²
21-100	5/clam ¹³

12-10 Gauge	Part #	Pkg Qty
-------------	--------	---------



20-1210	4/clam ¹²
---------	----------------------

¹²10 clams/master ¹³5 clams/master



GTB-406



GTB-408



GTB-410

Terminal Adapters

Part #	Pkg Qty	Gauge	Type
10-283F	100/bag	16-14 AWG	Female
10-285F	100/bag	12-10 AWG	Female

