

## Economy Electric Pumps

### PE20D & PE22J

- Lightweight - 22 - 41 lbs.
- 115 V AC 50/60 cycle universal motor works well with long extension cords or generator-driven power.
- Long 10' remote control for operator safety.
- Great for medium-sized cylinders.

	PE20D	PE22J
Motor Size	1/2 hp	1/2 hp
Type	Economy	Economy
Reservoir Capacity	1 gallon	1 gallon
Pump Type	Single-Acting	Single-Acting
Pressure Rating		
1st stage (psi)	200	200
2nd stage (psi)	10,000	10,000
Output Flow Rate		
1st stage (in <sup>3</sup> /min)	200	200
2nd stage (in <sup>3</sup> /min)	20	20
Valve Type	Dump	3-way, 2 pos.
Current Draw (Amps)	9.5	9.5
Motor Voltage (VAC)	115	115
Sound (dba)	85	85
Weight	29 lbs	27 lbs

### Single-Acting Pump

PE20D  
1/2 HP Pump



### Single-Acting Pump

PE22J  
1/2 HP Pump



### PE20D or PE22J Economy Electric Pumps

