



DRIVEN BY POSSIBILITY™

POWER ROUND™ & ROUND ENDLESS

WRAPPED, ROUND PROFILE BELT







Power Round belts are designed for more demanding applications. Round endless (standard) are designed to provide optimal grip in a low-torque application and are able to steadily maintain rotating parts in your power transmission systems with virtually no maintenance or re-tensioning.

CONSTRUCTION + SPECIFICATIONS

- **Flex-Bonded cords** are chemically forged to the belt body, providing equal load distribution and bending stress absorption without cord deterioration.
- **Flex-Weave™** oil and heat resistant cover protects the belt core from the toughest environments. The Power Round variant is a Double Layer cover for extended protection.
- **Power Round** variant also features an Alignment Stripe that runs the entire length of the belt to aid in eliminating belt twist during installation.

FEATURES + BENEFITS

- Power Round and Round Endless belts are ideal for quarter-turn or twisted drives, serpentine drives, power turn and line shaft conveyors and commercial sewing machines.
- Minimal stretch for minimum take-up requirements.
- No splice for added durability.
- Meets ARPM/RMA IP-3-2 oil and heat resistant standards.
- Meets ARPM/RMA IP-3-3 static conductivity requirements.
- REACH and RoHS 2 compliant.
- Operating temperature range: -30°C/-22°F to +82°C/180°F.

Belt Identification Chart			
	1/4"		7/16"
	5/16"		1/2"
	3/8"		9/16"

BELT IDENTIFICATION

Power Round: **9 X 54 PR**
9 - Belt Diameter in 1/16 inch (9/16")
54 - Inside Length (in)
PR - Power Round

Available Power Round Stock Sizes
9/16" 41-660 (in)

Round Endless: **6 X 44 RE**
6 - Belt Diameter in 1/16 inch (3/8")
44 - Inside Length (in)
RE - Round Endless

Available Round Endless Stock Sizes
1/4" 33-85 (in)
5/16" 33-90 (in)
3/8" 33-120 (in)
7/16" 33-106 (in)
1/2" 68-106 (in)
9/16" 41-660 (in)

