

SOLID STATE RELAY GRS-H SERIES



Up to 30A
with integrated diagnostics
only 17.5mm (0.69in)

GEFRAN
BEYOND TECHNOLOGY

SOLID STATE RELAY

COMPACT AND RELIABLE WITH INTEGRATED DIAGNOSTICS



**DIGITAL CONTROL
VDC/VAC**



**ZERO CROSSING
FIRING MODE**



**THERMAL
ALARM**



**LOAD BREAK
ALARM**



**EFFICIENTE HEAT
DISSIPATION**



**PUSH-IN
TERMINALS**



15A / 25A



30A



40A / 50A



60A / 75A



90A / 120A

GRS-H

CURRENT	15A / 25A	30A	40A / 50A	60A / 75A	90A / 120A
Voltage	24...660 Vac	24...660 Vac	24...660 Vac	24...660 Vac	24...660 Vac
Dimension mm(in)	17.5 x 110 x 107 (0.69 x 4.33 x 4.22)	17.5 x 110 x 142 (0.69 x 4.33 x 5.60)	35 x 110 x 142 (1.38 x 4.33 x 5.60)	70 x 110 x 142 (2.76 x 4.33 x 5.60)	70 x 140 x 142 (2.76 x 5.52 x 5.60)
Diagnostics	X	X	X	X	X
Fan cooling					X